

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


E

REV / 0L20-0282-97

13JAN98

ME

SB



1. STAMP AMP 16-14 APPROX AS SHOWN
2. WIRE INSUL DIA, 3.05-4.32 [0.120-0.170]
3. TONGUE MATL THK, 0.79±0.05 [0.031±0.002]

1000

LOOSE PIECE

322341

QTY


PACKAGE TYPE

PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
649°C [1200°F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm [in]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [0.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-MATERIAL
BODY, NI PER ASTM B162
SLEEVE, NI SIL PER
ASTM B122DWN
L OLMEDA

100CT94

CHK
M ELLIS

100CT94

APVD
S BORTNER

100CT94

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

AMPAMP Incorporated
Harrisburg, PA 17105-3608NAME
TERMINAL, RING TONGUE,
STRATOTHERM, DIAMOND GRIP,
WIRE SIZE, 16-14 AWG

SIZE

CAGE CODE

DRAWING NO

A3

00779

C-322341

SCALE
4:1SHEET
1 OF 1REV
EFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

CIRCULAR MIL AREA:
1.04mm²-2.62mm² [2050-5180]

STRANDED WIRE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[322341](#)