



AMP WIRE RANGE	IL E13288 Listed
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED
LR7189 Certified SOLID OR STRANDED	MILITARY P/N AND CLASS NOT APPLICABLE



1 STAMP AMP 22-18\* APPROX AS SHOWN  
22-16 TERMINALS ARE STAMPED 22-18 IN  
ACCORDANCE WITH MILITARY SPECIFICATION  
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED  
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING  
TEMPERATURE: 170°C MAX

VOLTAGE RATING:  
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:  
0.26-1.65mm² [509-3,260] CIR MILS  
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR  
AMP INCORPORATED. IT IS SUBJECT TO CHANGE  
AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.  
UNLESS SPECIFIED  
DIMENSIONS IN mm [INCHES]  
TOLERANCES ON:  
2 PLG DEC ±  
3 PLG DEC ±  
ANGLES ±

MATERIAL  
COPPER PER  
ASTM B-152  
ANNEALED

FINISH TIN PLATE  
0.00254 [1.000100] MIN  
THK PER MIL-T-10727

DR 3-10-93  
TA BRINKMAN

CHK 3-10-93  
DA PATTERSON

APPD 3-10-93  
DE MILLER

APPD 3-10-93  
JL MECKLEY

PRODUCT SPEC

APPLICATION SPEC

AMP  
AMP Incorporated  
Harrisburg, PA 17105-3608

TERMINAL, RING  
TONGUE, SOLISTRAND™

SIZE CAGE CODE DRAWING NO  
G 00779 G-329966  
SCALE 8:1 SHEET 1 OF 1

100	LOOSE PIECE, BOX	8-329966-1
---	LOOSE PIECE	329966
QUANTITY	PACKAGE TYPE	PART NO

329966

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-329966-1](#)