




LOC		DIST		REV		DATE		APPRO	
G	14	P	F	ZONE	LTR	DESCRIPTION	0720-0040-93	3-9-93	1st DAP



STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928; COMMERCIAL WIRE RANGE IS 22-16

AMP WIRE RANGE		E13288 Listed	
22-16 AWG	SOLID OR STRANDED	22-16 AWG	SOLID OR STRANDED
LR7189 Certified		MILITARY P/N AND CLASS	
22-16 AWG	SOLID OR STRANDED	M7928/7-1 CLASS 2	PN'S 34103 & 2-34103-1

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION
1-800-722-1111

FOR ORDER ENTRY
1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
0.26-1.65mm² [509-3.260] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
WITHOUT NOTICE. REVISED EDITIONS
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLG DEC ±
3 PLG DEC ±
ANGLES ±
MATERIAL
COPPER PER
ASTM B-152
ANNEALED

FINISH
TIN PLATE
0.00254 [0.00100] MIN
THK PER MIL-T-10727

DR 1-27-93
TA BRINKMAN
CHK 1-27-93
DA PATTERSON

APPD 1-27-93
DE MILLER
APPD 1-27-93
JL MECKLEY
PRODUCT SPEC

APPLICATION SPEC

WEIGHT

5000	ON TAPE	2-34103-1
---	LOOSE PIECE	34103
QUANTITY		PART NO

TERMINAL, RING
TONGUE, SOLISTRAND™

AMP Incorporated
Harrisburg, PA 17105-3608

SIZE
CAGE CODE
DRAWING NO
SCALE 10:1

00779
34103

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[34103](#)