




LOC		DIST		REV		DATE		APPRO	
G	14	P	F	ZONE	LTR	DESCRIPTION	0720-0040-93	3-9-93	1st DAP



STAMP AMP 22-18\* APPROX AS SHOWN  
22-16 TERMINALS ARE STAMPED 22-18 IN  
ACCORDANCE WITH MILITARY SPECIFICATION  
MIL-T-7928; COMMERCIAL WIRE RANGE IS 22-16

AMP WIRE RANGE		E13288 Listed	
22-16 AWG	SOLID OR STRANDED	22-16 AWG	SOLID OR STRANDED
LR7189 Certified		MILITARY P/N AND CLASS	
22-16 AWG	SOLID OR STRANDED	M7928/7-1 CLASS 2	PN'S 34103 & 2-34103-1

# AMP INCORPORATED CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL  
PRODUCT INFORMATION OR  
COPIES OF DRAWINGS  
AND TECHNICAL DOCUMENTS  
1-800-522-6752

FOR APPLICATION  
TOOLING INFORMATION  
1-800-722-1111

FOR ORDER ENTRY  
1-800-526-5142

MAX RECOMMENDED OPERATING  
TEMPERATURE:  
170°C MAX

VOLTAGE RATING:  
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:  
0.26-1.65mm<sup>2</sup> [509-3.260] CIR MILS

SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. REVISED EDITIONS SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.  
UNLESS SPECIFIED  
DIMENSIONS IN mm [INCHES]  
TOLERANCES ON:  
2 PLG DEC ±  
3 PLG DEC ±  
ANGLES ±  
MATERIAL  
COPPER PER  
ASTM B-152  
ANNEALED

FINISH  
TIN PLATE  
0.00254 [0.00100] MIN  
THK PER MIL-T-10727

DR 1-27-93  
TA BRINKMAN  
CHK 1-27-93  
DA PATTERSON  
APPD 1-27-93  
DE MILLER  
APPD 1-27-93  
JL MECKLEY  
PRODUCT SPEC

NAME



AMP Incorporated  
Harrisburg, PA 17105-3608

TERMINAL, RING  
TONGUE, SOLISTRAND™

SIZE  
CAGE CODE  
00779  
DRAWING NO  
34103

SCALE 10:1

SHEET 1 OF 1

QUANTITY		PACKAGING TYPE		PART NO	
5000	ON TAPE	2-34103-1			
---	LOOSE PIECE	34103			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-34103-1](#)