


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
		P1		REVISED PER ECO-11-004820	11MAR11	RK HMR

AMP WIRE RANGE	 Listed	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- 1

STAMP AMP 16-14* APPROX AS SHOWN
- 2

WIRE INSULATION DIA: 3.00-4.90 [.118-.193]
- 3

TONGUE MATERIAL THK: 0.79^{±0.05} [.031^{±.002}]
- 4

MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - BLUE
- 5

MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - BLACK
- 6

REPLACED BY 34163

OBSOLETE

25	LOOSE PIECE, BAG	4	8-34163-5
100	LOOSE PIECE, BOX	4	8-34163-1
6 OBSOLETE	LOOSE PIECE	5	2-34163-2
4000	ON TAPE, REEL	4	2-34163-1
-	LOOSE PIECE	4	34163
QTY	PACKAGE TYPE	PART NO.	

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221° F]		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 08/06/92		 TE Connectivity										
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A		DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK RE HERSEY 11/10/92		APVD M ELLIS 11/10/92			NAME					
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] SOLID OR STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1034		APPLICATION SPEC NOT AVAILABLE			SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL SEE NOTES		FINISH TIN PER ASTM B545		WEIGHT -		A3		00779		C-34163		-		
										CUSTOMER DRAWING					SCALE 4:1		SHEET 1 OF 1		REV P1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-34163-1](#)