



REVISIONS				DESCRIPTION	DATE	APPROVED
1						



AMP WIRE RANGE		UL E13288 Listed	
12-10 AWG STRANDED		12-10 AWG STRANDED	
NOT CERTIFIED		MILITARY P/N AND CLASS	
NOT CERTIFIED		NOT APPLICABLE	

△ STAMP AMP 12-10* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:	170°C MAX
VOLTAGE RATING:	NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE:	2.62-6.64mm² (5,180-13,100) CIR MILS STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR THE CUSTOMER SERVICE SYSTEMS DIVISION. IT IS THE PROPERTY OF AMP INCORPORATED AND IS NOT TO BE REPRODUCED OR COPIED WITHOUT THE WRITTEN PERMISSION OF AMP INCORPORATED. ANY UNAUTHORIZED REPRODUCTION OR COPIING OF THIS DRAWING IS PROHIBITED AND WILL BE CONSIDERED A VIOLATION OF THE COMPANY'S POLICY. THE LATEST REVISION SHOULD BE CONSULTED FOR THE LATEST DESIGN.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES - TOLERANCES ON: 2 PLC DEC ± .005 3 PLC DEC ± .002 ANGLES ± .5°	DR 3-5-93 TA BRINKMAN CHK 3-5-93 DA PATTERSON APD 3-5-93 DE MILLER APD 3-5-93 JL HECKLEY PRODUCT SPEC
---	---

FINISH: TIN PLATE 0.0025±(L.000100) MIN THK PER MIL-T-10727	APPLICATION SPEC
---	------------------

AMP INCORPORATED Harrisburg, PA 17125-3508	34891 PART NO
---	------------------

TERMINAL, RING TONGUE,
BUDGET

SIZE	CAGE CODE	DRAWING NO
SCALE 8:1	00779	C-34891
WEIGHT		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[34891](#)