



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REV PER 0G3A-0567-01	16OCT01	—	JR
	C1	REVISED PER ECO-17-008806	16FEB2018	RS	DR



AMP WIRE RANGE	E13288 Listed
12-10 AWG STRANDED	12-10 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

- 1

STAMP AMP 12-10* APPROX AS SHOWN
- 2

NOTE DELETED

500	LOOSE PIECE	34964
QTY	PACKAGE TYPE	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 2-3-93		 TE Connectivity Ltd.							
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER	MAX RECOMMENDED OPERATING TEMPERATURE:	DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK DA PATTERSON 2-3-93	NAME TERMINAL, RING TONGUE BUDGET 12-10 AWG						
	1-800-522-6752	170°C [338°F] MAX			0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± -							APVD DE MILLER 2-3-93		
	VOLTAGE RATING:	NOT APPLICABLE			ANGLES ± -									
FOR APPLICATION	TOOLING ASSISTANCE CENTER	WIRE CROSS SECTIONAL AREA RANGE, 2.62-6.64mm²[5,180-13,100] CIR MILS SOLID OR STRANDED	MATERIAL		FINISH	APPLICATION SPEC —	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
TOOLING INFORMATION	1-800-722-1111							A2	00779	C=34964	—			
FOR ORDER ENTRY	1-800-526-5142					CUSTOMER DRAWING			SCALE	10:1	SHEET	1 of 1	REV	C1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[34964](#)