


4

3


2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	25		J2	ECO-06-017742	27JUL06	BSV	DC



12.70±0.38  
[.500±.015]



0.81±0.13  
[.032±.005]

1. MAX BUNDLE RANGE: 9.53[.375] TO 101.60[4.000].
2. WEIGHT PER 304.8M[1000ft]: 10.44kg[23lb].
- 3

SEE RESTRICTED CUSTOMER DRAWING 500037-4.
4. OVERALL LENGTH TO BE WITHIN +1 Ft -0 Ft.
5. ONE SPLICE PER BOX IS ALLOWABLE.

—	—	<div>3</div>
15.24M[50ft]BOX	BLACK	500037-1
LENGTH	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.CHANDLER	16DEC93	<div><div>tyco</div><div>Electronics</div></div>		Tyco Electronics Corporation		
		CHK —	—			Harrisburg, Pa 17105-3608		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. KAAT	16DEC93	NAME			
	0 PLC ± -		PRODUCT SPEC	SPIRAP, NYLON OUTDOOR, 1/2 INCH DIAMETER				
	1 PLC ± -		—					
	2 PLC ± -		APPLICATION SPEC					
	3 PLC ± -		—					
	4 PLC ± -				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	ANGLES ± -				A3	00779	C-500037	—
MATERIAL NYLON	FINISH —		WEIGHT —					
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 OF 1	REV J2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[500037-1](#)