



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P4	REVISED PER ECO-15-016493	30NOV2015	NK	DR
	P5	REVISED PER ECO-17-016703	30MAR2018	RS	DR

- 1
- STAMP AMP, APPROX AS SHOWN
- 2
- BODY MATERIAL THK: 0.457±0.051[.018±.002]
- 3
- BODY: COPPER ASTM B152 NICKEL PL
SAE AMS QQ-N-290 0.0076 [.0003] AVG EXT. THK
- 4
- SLEEVE: COPPER ASTM B152 NICKEL PL
SAE AMS QQ-N-290 0.00076 [.00003] AVG EXT. THK
- 5
- INSULATION: PTFE ASTM D3295
COLOR - BLACK
- 6
- FOR 0.813[.032] TO 2.083[.082] WIRE INSULATION DIA.
- 7
- NOTE DELETED
- 8
- DIMENSION APPLIES FROM EDGE OF METAL
WIRE BARREL TO CENTER OF STUD HOLE

5	1000	3.683[.145]	M3.5[#6]	LOOSE PIECE	50830
	QTY	"A"	"B"	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 288°C [550°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 11AUG03	 TE Connectivity Ltd.		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK T MICHIELUTTI 12AUG03			
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.12-0.24mm² [238-475] STRANDED WIRE ONLY		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± 1°	APVD T MICHIELUTTI 12AUG03	NAME TERMINAL, RING TONGUE, PIDG, STRATO-THERM, 26-24 AWG		
FOR ORDER ENTRY	1-800-526-5142		MATERIAL 3 4 5	FINISH 3 4 5	PRODUCT SPEC —	SIZE A3	CAGE CODE 00779	DRAWING NO C-50830
CUSTOMER DRAWING						RESTRICTED TO —	SCALE 8:1	
						SHEET 1 OF 1	REV P5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[50830](#)