





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L1	REV PER ECO-12-014455	13SEP12	KH	DR
	L2	REVISED PER ECO-17-014338	29MAR2018	RS	DR

<b>AMP</b> WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- 1 STAMP 8SAMP 16-14\* APPROX AS SHOWN
- 2 WIRE INSUL DIA, 2.997-4.902 [.118-.193]
- 3 BODY MATL THK, 0.787±0.051 [.031±.002]
- 4 MATERIAL: BODY - BRASS PER ASTM B36  
INSULATION - PVC
- 5 APPLIES FROM CENTER OF STUD HOLE TO  
EDGE OF METAL WIRE BARREL

5000	ON TAPE, REEL	52464-1
1000	LOOSE PIECE	52464
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE:  105°C [221° F]		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN L OLMEDA 26JUN95		 TE Connectivity Ltd.											
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER  1-800-522-6752		VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)		DIMENSIONS:  mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK M ELLIS 26JUN95		NAME									
FOR APPLICATION  TOOLING INFORMATION		TOOLING ASSISTANCE CENTER  1-800-722-1111		CIRCULAR MIL AREA:  1.04-2.62mm² [2,050-5,180] SOLID OR STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		APVD G NGO 26JUN95		TERMINAL, SPRING SPADE, LONG, PLASTI-GRIP, WIRE SIZE: 16-14 AWG									
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL 		FINISH  BODY: TIN PER ASTM B545 INSULATION: COLOR-BLUE		PRODUCT SPEC  UL 486A-B		APPLICATION SPEC  114-2161		SIZE A3		CAGE CODE 00779		DRAWING NO C-52464		RESTRICTED TO  -	
										WEIGHT		CUSTOMER DRAWING				SCALE 6:1		SHEET 1 OF 1		REV L2	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[52464-1](#)