



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REV, RDRW, & SM PKG PER 0720-0040-93	9-26-93	TAB	DAP
	B1	REVISED PER ECO-17-008808	03MAR2018	RS	DR



AMP WIRE RANGE	E13288 Listed
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
22-16 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
SAE AS7928, COMMERCIAL WIRE RANGE IS 22-16



100	LOOSE PIECE, BOX	8-53555-1
1000	LOOSE PIECE	53555-1
QUANTITY	PACKAGING TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN TA BRINKMAN 3-26-93		 TE Connectivity Ltd.			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER	1-800-522-6752	DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK DA PATTERSON 3-26-93					
	MAX RECOMMENDED OPERATING TEMPERATURE:	170°C [338°F] MAX	APVD DE MILLER 3-26-93		NAME TERMINAL, SPADE TONGUE, SOLISTRAND™ 22-16 AWG						
	VOLTAGE RATING:	NOT APPLICABLE	PRODUCT SPEC UL 486 A-B			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
FOR APPLICATION	TOOLING ASSISTANCE CENTER	1-800-722-1111	MATERIAL COPPER PER ASTM B-152 ANNEALED		FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B545	APPLICATION SPEC —	WEIGHT —	A2	00779	C=53555	—
TOOLING INFORMATION	1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE, 0.26-1.65mm²[509-3,260] CIR MILS SOLID OR STRANDED									
FOR ORDER ENTRY	1-800-526-5142		CUSTOMER DRAWING			SCALE 10:1		SHEET 1 of 1	REV B1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-53555-1](#)