


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REV/ 0720-0612-95	31MAY95	-	ME
	C1	REVISED PER ECO-17-014338	29MAR2018	RS	DR
	C2	REVISED PER ECO-20-017411	10DEC2020	RK	DR

E13288  
Listed

16-14 AWG  
SOLID OR STRANDED



1. WIRE INSUL DIA, 2.921-4.318 [.115-.170]
- 2 INSULATION STRIPES: 2 - 180 DEGREES APART.
- 3 MATERIAL: BODY - COPPER PER ASTM B152  
INSULATION - PVC
- 4 FINISH: BODY - TIN PLATE 0.00254 [.000100] MIN  
EXT THK PER ASTM B545  
INSULATION COLOR - TRANSPARENT BLUE  
INSULATION STRIPE COLOR - BLUE

2500	ON TAPE, REEL	55785-2
1000	LOOSE PIECE	55785-1
QTY	PACKAGE TYPE	PART NO


MAX RECOMMENDED OPERATING TEMPERATURE:  
105°C [221° F]

VOLTAGE RATING:  
600V MAX  
(1000V FIXTURE OR SIGN)

CIRVULAR MIL AREA:  
1.04-2.62mm²[2.050-5.180]  
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]




MATERIAL  
3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± 0.127[.005]  
4 PLC ± -  
ANGLES ± -  
FINISH 4

DWN DK SCHRUM 4/12/90  
CHK MS FEHER 4/16/90  
APVD TL SHUTTER 4/17/90  
PRODUCT SPEC  
UL 486A-B  
APPLICATION SPEC  
114-2161  
WEIGHT -

TE Connectivity

NAME  
SPLICE, BUTT, PLASTI-GRIP,  
WIRE SIZE, 16-14 AWG  
-

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C-55785

RESTRICTED TO  
-

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV C2

1470-19 (1/15)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55785-1](#)