


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REV/ 0720-0612-95	31MAY95	—	ME
	E1	REVISED PER ECO-17-014338	29MAR2018	RS	DR

E13288
Listed

22-16 AWG
SOLID OR STRANDED




1. WIRE INSUL DIA, 2.667-3.556 [.105-.140]

2500	ON TAPE, REEL	BODY: COPPER PER ASTM B-152 TIN PL 0.00254[.000100] MIN THK PER ASTM B545	55792-2
1000	LOOSE PIECE	INSULATION: VINYL COLOR: TRANSPARENT	55792-1
QTY	PACKAGE TYPE	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .127[.005]
4 PLC ± -
ANGLES ± -

FINISH
SEE TABLE

DWN
DK SCHRUM
9/14/90

CHK
MS FEHER
9/14/90

APVD
TL SHUTTER
9/14/90

PRODUCT SPEC
UL 486A-B

APPLICATION SPEC
114-2161

WEIGHT

TE Connectivity Ltd.

NAME
SPLICE, BUTT, PLASTI-GRIP,
WIRE SIZE, 22-16 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-55792

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
5:1

SHEET
1 OF 1

REV
E1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55792-2](#)