


- CONTACT: 0.00076 GOLD AT INTERFACE. 0.00254 MIN MATTE TIN ON SOLDER TAIL. 0.00127 MIN NICKEL UNDERPLATE ALL OVER.
2. MATES WITH AMP-DUAC/PL PLUG RECEPTACLE 794152 AND ITS CONTACTS.
- CLEARANCE ENVELOPE FOR MATING PLUG RECEPTACLE LATCH.
- ALL POSTS STANDARD.
- CONTACT GROUND POST LOCATED IN CIRCUIT 3, ASSEMBLY P/N 5794172-3.
7. NO POST IN POSITION 1
8. NO POST IN POSITION 2
9. NO POST IN POSITION 4

RECOMMENDED MOUNTING HOLE PATTERN FOR 1.78 MAX THICK P.C. BOARD COMPONENT SIDE SHOWN SCALE 4:1


5794172-3 SHOWN

- OBSOLETE 9
- OBSOLETE 8
- OBSOLETE 7
- OBSOLETE 6
- OBSOLETE 5

BRASS		PBT, UL94V-0	NATURAL(WHITE)	5794172-6
BRASS		PBT, UL94V-0	NATURAL(WHITE)	5794172-5
BRASS		PBT, UL94V-0	NATURAL(WHITE)	5794172-4
BRASS		PBT, UL94V-0	NATURAL(WHITE)	5794172-3
BRASS		PBT, UL94V-0	NATURAL(WHITE)	5794172-2
MATERIAL	FINISH	MATERIAL	COLOR	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		
		0 PLC ± -		
		1 PLC ± 0.2		
		2 PLC ± 0.13		
		3 PLC ± -		
		4 PLC ± -		
		ANGLES ± 8° 30'		
MATERIAL SEE TABLE		FINISH SEE TABLE		
		WEIGHT -		
		CUSTOMER DRAWING		
		SCALE 5:1		
		SHEET 1 OF 1		
		REV A2		



3-DIMENSIONAL MODEL NTS



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5794172-4](#) [5794172-6](#) [5794172-5](#)