








	OBSOLETE		3	49.89 [1.964]	29.74 [1.171]	1-66470-1
	OBSOLETE		1	37.97 [1.495]	17.81 [.701]	1-66470-0
			3	49.89 [1.964]	29.74 [1.171]	66470-9
	SUPERSEDED		1	37.97 [1.495]	17.81 [.701]	66470-7
		POST PLATING	NO OF TERM	B	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.REIFSNYDER 07 JUN 96		 TE Connectivity	
		CHK R.STONE 12 JUL 96			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.25[.010] 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME PIN CONTACT, CRIMPED, .062 DIA, .031 x .062 POST, WRAP TYPE	
		APVD G.STEINHAUER 23 JUL 96 PRODUCT SPEC — APPLICATION SPEC —		SIZE A2	
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS		CAGE CODE 00779	
		WEIGHT —		DRAWING NO G-66470	
		CUSTOMER DRAWING		RESTRICTED TO —	
				SCALE 4:1	
				SHEET 1 of 1	
				REV N2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[66470-9](#)