

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	K	REDRAWN PER ECR-17-012487	19NOV2018	BDA	SG
	K1	REDRAWN PER ECR-20-100305	13AUG2020	PJ	VS

- 1

0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
- 2






WIRE RANGE: 0.3-0.9MM²(22-18 AWG).
- 3

INSULATION RANGE: 1.50-2.39[.059-.094] DIA.
- 4

DIMENSIONS IN BRACKETS ARE IN INCHES.

- 5

0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



	0.25[.010] BRASS	1-794221-0
	0.25[.010] BRASS	794221-3
PRE TIN	0.25[.010] BRASS	794221-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. VESTAL 1-15-97		 TE Connectivity		
			CHK R. SWING 1-15-97	NAME			
			APVD B. SWING 1-15-97	PRODUCT SPEC			
				APPLICATION SPEC			
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:			SOCKET, MINI UNIVERSAL MATE-N-LOK 2		
		0 PLC ±					
		1 PLC ±					
		2 PLC ±					
		3 PLC ±					
		±0.30 [0.012]			RESTRICTED TO		
		4 PLC ±					
		ANGLES					
		FINISH					
MATERIAL SEE TABLE		SEE TABLE		WEIGHT	SIZE CAGE CODE DRAWING NO		
-		-		-	A1 00779 ©=794221		
CUSTOMER DRAWING				SCALE		SHEET 1 OF 1	
				5:1		REV K1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[794221-1 \(Mouser Reel\)](#)