




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	4	REVISED PER ECR-20-010947	04AUG2020	GK	AK



NOTES:

- 1 FOR PART NUMBER SEE SHEET 3 OF 3.
- 2 MARK SHOULD BE CENTRALLY POSITIONED ± 0.1 mm.
- 3 WIDTH OF MARK DEPENDS ON CHARACTER PRINTED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K 22MAR2013		 TE Connectivity							
		CHK KEAN ALAN 22MAR2013									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME							
				SNAP-ON MARKER STB/STD SIZE 15 WITH APPLICATOR							
				—							
				—							
MATERIAL —		FINISH —		SIZE		CAGE CODE	DRAWING NO		RESTRICTED TO		
				A3		C2290	C-7-1768045-4		—		
				CUSTOMER DRAWING							
				SCALE		NTS		SHEET	1 OF 3	REV	4

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22MAR2013 RAGHAVENDRA K CHK 22MAR2013 KEAN ALAN APVD 22MAR2013 MARIO APPELLO PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		<div>TE Connectivity</div>									
DIMENSIONS: mm		<div><div><div>0 PLC ± —</div><div>1 PLC ± —</div><div>2 PLC ± —</div><div>3 PLC ± —</div><div>4 PLC ± —</div><div>ANGLES ± —</div></div><div>± —</div></div>		NAME SNAP-ON MARKER STB/STD SIZE 15 WITH APPLICATOR — —									
				SIZE A3		CAGE CODE C2290		DRAWING NO G-7-1768045-4		RESTRICTED TO —			
MATERIAL —		FINISH —		CUSTOMER DRAWING				SCALE NTS		SHEET 2 OF 3		REV 4	

REVISIONS

DESCRIPTION	DATE	DWN	APVD
	—	—	—

DESCRIPTION	PART NO.
STD15Y—COLON	9—1768045—1
STD15Y—D	9—1768045—2
STD15Y—DOT	9—1768045—4
STD15Y—E	9—1768045—5
STD15Y—EARTH	9—1768045—6
STD15Y—F	9—1768045—8
STD15Y—G	1768046—1
STD15Y—H	1768046—3
STD15Y—I	1768046—5
STD15Y—J	1768046—6
STD15Y—K	1768046—7
STD15Y—L	1768046—9
STD15Y—M	1—1768046—1
STD15Y—MINUS	1—1768046—2
STD15Y—N	1—1768046—4
STD15Y—P	1—1768046—6
STD15Y—PLUS	1—1768046—7
STD15Y—Q	1—1768046—8
STD15Y—R	1—1768046—9
STD15Y—S	2—1768046—1
STD15Y—SLASH	2—1768046—2
STD15Y—T	2—1768046—3
STD15Y—U	2—1768046—4
STD15Y—V	2—1768046—5
STD15Y—W	2—1768046—6
STD15Y—X	2—1768046—7
STD15Y—Y	2—1768046—8
STD15Y—Z	2—1768046—9
STD15Y—AC	8—1768045—5

TE

TE Connectivity

—ON MARKER STB/STD SIZE 15 WITH APPLICATION

—

—



CAGE CODE	DRAWING NO	RESTRICTED TO
C2290	<div><div>C</div><div>7—1768045—4</div></div>	—
	SCALE	SHEET
	NTS	3 OF 3
		REV
		4

DESCRIPTION	PART NO.
STB15-0-0	6-1768039-0
STB15-1-1	6-1768039-1
STB15-1-2	2-1768413-1
STB15-1-3	9-1768412-3
STB15-1-5	6-1768039-2
STB15-2-2	6-1768039-4
STB15-2-5	6-1768039-5
STB15-3-2	2-1768413-2
STB15-3-3	6-1768039-7
STB15-4-2	2-1768413-3
STB15-5-2	2-1768413-4
STB15-5-5	7-1768039-0
STB15-6-6	7-1768039-2
STB15-7-7	7-1768039-3
STB15-8-8	7-1768039-6
STB15-A-3	7-1768039-7
STB15-A-5	7-1768039-8
STB15-BLANK-0	8-1768039-0
STB15-BLANK-1	8-1768039-1
STB15-BLANK-2	8-1768039-2
STB15-BLANK-3	8-1768039-3
STB15-BLANK-5	8-1768039-4
STB15-BLANK-6	8-1768039-5
STB15-BLANK-7	8-1768039-6
STB15-BLANK-8	8-1768039-7
STB15-F-6	8-1768039-9
STB15-H-2	9-1768039-0
STB15-H-5	7-1768418-2
STB15-L-5	9-1768039-2
STB15-R-0	9-1768039-6
STB15-R-5	9-1768039-8
STB15-S-5	7-1768418-3
STB15-0-2	2-1768413-0
STB15-6-2	2-1768413-5
STB15-7-2	2-1768413-6
STB15-9-2	2-1768413-8
STB15-B-5	7-1768039-9
STD15W-AC	5-1768045-6

DESCRIPTION	PART NO.
STB15-T-6	1768040-1
STB15-V-6	1768040-3
STD15-APPLICATOR	5-1768045-4
STD15W-0	5-1768045-5
STD15W-1	916500-000
STD15W-2	631526-000
STD15W-3	883382-000
STD15W-4	924992-000
STD15W-5	381396-000
STD15W-6	545292-000
STD15W-7	360170-000
STD15W-8	075056-000
STD15W-9	054712-000
STD15W-A	755008-000
STD15W-A-LC	5-1768045-7
STD15W-B	802902-000
STD15W-BLANK	5-1768045-8
STD15W-C	838714-000
STD15W-D	629606-000
STD15W-D-LC	6-1768045-0
STD15W-DOT	6-1768045-1
STD15W-E	133110-000
STD15W-EARTH	6-1768045-2
STD15W-F	537002-000
STD15W-G	685362-000
STD15W-H	863976-000
STD15W-H-LC	6-1768045-2
STD15W-I	913588-000
STD15W-J	344640-000
STD15W-K	501372-000
STD15W-L	002648-000
STD15W-COLON	126530-000

DESCRIPTION	PART NO.
STD15W-M	347828-000
STD15W-MINUS	6-1768045-9
STD15W-N	612672-000
STD15W-P	388482-000
STD15W-PLUS	7-1768045-2
STD15W-Q	621494-000
STD15W-R	325234-000
STD15W-S	544426-000
STD15W-SLASH	857128-000
STD15W-T	845482-000
STD15W-U	126270-000
STD15W-V	907764-000
STD15W-W	071812-000
STD15W-X	362816-000
STD15W-Y	578440-000
STD15W-Z	063698-000
STD15Y-0	7-1768045-4
STD15Y-1	7-1768045-5
STD15Y-2	7-1768045-6
STD15Y-3	7-1768045-7
STD15Y-4	7-1768045-8
STD15Y-5	7-1768045-9
STD15Y-6	8-1768045-0
STD15Y-7	8-1768045-1
STD15Y-8	8-1768045-2
STD15Y-9	8-1768045-3
STD15Y-A	8-1768045-4
STD15Y-B	8-1768045-7
STD15Y-BLANK	8-1768045-8
STD15Y-C	9-1768045-0

DESCRIPTION	PART NO.
STD15Y-COLON	9-1768045-1
STD15Y-D	9-1768045-2
STD15Y-DOT	9-1768045-4
STD15Y-E	9-1768045-5
STD15Y-EARTH	9-1768045-6
STD15Y-F	9-1768045-8
STD15Y-G	1768046-1
STD15Y-H	1768046-3
STD15Y-I	1768046-5
STD15Y-J	1768046-6
STD15Y-K	1768046-7
STD15Y-L	1768046-9
STD15Y-M	1-1768046-1
STD15Y-MINUS	1-1768046-2
STD15Y-N	1-1768046-4
STD15Y-P	1-1768046-6
STD15Y-PLUS	1-1768046-7
STD15Y-Q	1-1768046-8
STD15Y-R	1-1768046-9
STD15Y-S	2-1768046-1
STD15Y-SLASH	2-1768046-2
STD15Y-T	2-1768046-3
STD15Y-U	2-1768046-4
STD15Y-V	2-1768046-5
STD15Y-W	2-1768046-6
STD15Y-X	2-1768046-7
STD15Y-Y	2-1768046-8
STD15Y-Z	2-1768046-9
STD15Y-AC	8-1768045-5

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22MAR2013 RAGHAVENDRA K CHK 22MAR2013 KEAN ALAN		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD 22MAR2013 MARIO APPELLO		NAME SNAP-ON MARKER STB/STD SIZE 15 WITH APPLICATOR	
		PRODUCT SPEC -		APPLICATION SPEC -		SIZE A3	
MATERIAL -		FINISH -		WEIGHT -		CAGE CODE C2290	
				DRAWING NO G-7-1768045-4		RESTRICTED TO -	
CUSTOMER DRAWING						SCALE NTS	
						SHEET 3 OF 3	
						REV 4	



OBSOLETE PART

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[STD15W-9](#)