


LOC	DIST	REVISIONS					
DF	S0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H	REV PER ECO-05-014991	06FEB06	PY	DE



- 1

TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
2.

MARKED PER MIL-STD-130.
3.

TO MATE WITH AMP LGH-1/2L
RECEPTACLE WITH .89 [22.6] BARREL DEPTH.
- 4

"B" DIMENSION IS SOLDER DIPPED.
5.

OPERATING VOLTAGE: 15 KVDC AT 0 TO 70,000 FEET, -55° C TO 125° C.
- 6

INSULATION CUT, BUT NOT REMOVED

	6	.38 [9.7]	15.00 [381.0]	5-863139-3
OBSOLETE	4	.38 [9.7]	24.00 [609.6]	863139-4
	4	.38 [9.7]	15.00 [381.0]	863139-3
OBSOLETE	4	.25 [6.3]	6.00 [152.4]	863139-2
OBSOLETE	4	.38 [9.7]	21.00 [533.4]	863139-1
REMARKS		B 4	A 1	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 12-20-89	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK D. EABY 12-20-89		
	0 PLC ± -	APVD -	NAME LEAD ASS'Y, SGL. END, LGH-1/2L	
	1 PLC ± -	PRODUCT SPEC -		
	2 PLC ± .02 [0.5]	APPLICATION SPEC -		
MATERIAL SEE CALLOUTS	3 PLC ± -	WEIGHT -	SIZE A2	CAGE CODE 00779
	4 PLC ± -	CUSTOMER DRAWING	DRAWING NO C=863139	RESTRICTED TO -
	ANGLES ± -		SCALE 4:1	SHEET 1 OF 1
		FINISH -	REV H	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[863139-3](#)