





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		K1	REVISED ECO-09-024927	06NOV09	KK	AEG



- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE OF BEAMS).
- 2 TOLERANCE NON-CUMULATIVE.
- 3 THE MATING END OF THE CONTACT IS IDENTIFIED BY THE LETTER "A" STAMPED ON THE RECEPTACLE BOX.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



4 OBSOLETE	3.120	2.964	20	-2=87988=0
	2.964	2.808	19	1-87988-9
4 OBSOLETE	2.808	2.652	18	-1=87988=8
	2.652	2.496	17	1-87988-7
OBSOLETE 4	2.496	2.340	16	-1=87988=6
	2.340	2.184	15	-1=87988=5
	2.184	2.028	14	-1=87988=4
	2.028	1.872	13	-1=87988=3
	1.872	1.716	12	-1=87988=2
	1.716	1.560	11	-1=87988=1
OBSOLETE 4	1.560	1.404	10	1-87988-0
	1.404	1.248	9	-87988=9-
	1.248	1.092	8	-87988=8-
	1.092	.936	7	87988-7
	.936	.780	6	87988-6
	.780	.624	5	87988-5
4 OBSOLETE	.624	.468	4	87988-4
	.468	.312	3	87988-3
	.312	.156	2	-87988=2-
B		A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

RECEPTACLE BOX, TYPE C, COLOR-BLACK, CONTACTS- PHOS. BRONZE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	.005
4 PLC	±	-
ANGLES	±	-

FINISH

.000030 GOLD TO CONTACT AREA, GOLD FLASH ON THE REMAINDER, ALL OVER .000050 NICKEL

DWN
L A MAYER
17MAR86

CHK
P deJONG
17MAR86

APVD
P deJONG
17MAR86

PRODUCT SPEC
108-25,016

APPLICATION SPEC
108-25,016

WEIGHT
-

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
ASSY, MOD I, BOARD MOUNT RECP,
.156 CL, STD PRESSURE, TYPE C,
FOR ROUND HOLE MOUNTING

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=87988

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
K1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[87988-5](#)