


NUMBER 917511
METRIC 三脚法(3rd ANGLE PROJECTION)

U.855-1112-U.DWG>S.CB9-25173
単位: mm DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST



注記

- △ 標準接圧型コンタクト：一般向け及び多極用
- △ 高接圧型コンタクト：高電流用及び強振動用
- △ 金めっきは接触部のみとする

NOTES

- △ CONTACT TYPE; NORMAL PRESSURE TYPE (FOR GENERAL)
- △ CONTACT TYPE; HIGH PRESSURE TYPE (FOR HIGH CURRENT OR ANTI-VIBRATION)
- △ GOLD-PL. CONTACT AREA ONLY

△	H	5	光沢錫めっき (BRIGHT TIN-PL.)	1-	-5	
		3	0.76μm最小金めっき (0.76μmMIN. Au-PL.)	1-	-3	
△		2	0.38μm最小金めっき (0.38μmMIN. Au-PL.)	1-	-2	
		3	0.76μm最小金めっき (0.76μmMIN. Au-PL.)		-3	
△		2	0.38μm最小金めっき (0.38μmMIN. Au-PL.)	917511-2		
		仕上 (FINISH)	仕上 (FINISH)	△	型番 (P/N)	
備考 (REMARK) 接圧表示 (ID-MARK) 接触タイプ (CONT. TYPE) 金めっきコード (PL. ID NO)						
 TE Connectivity						
線合電線断面積 (WIRE RANGE) AWG 16-14		線被外径 (INSULATION DIA.) 2.2-2.8 mm		名称 (NAME) DYNAMIC SERIES REC. CONTACT 2L" SIZE LOOSE PIECE ダイナミックシリーズリセブルコンタクト		
材料 (MATERIAL) (COPPER ALLOY) 銅合金		仕上 (FINISH) (SEE TABLE) 表参照				
一般公差 (GENERAL TOLERANCE) 10±0.2 10±0.25 30±0.3 30±0.35		SIZE B J		号 (No.) 917511		
LTR 実測 (REVISION RECORD)		DR. 27/APR/95 K. IKEDA		DE. 27/APR/95 K. IKEDA		
B REVISED PER ECR-15-011723 Y.O. E.T. 05AUG 2015		APP. 28/APR/95 S. MANABE		APP. 28/APR/95 S. MANABE		
A1 REVISED PER ECO-11-005294 RK HMR 07APR 11						
LTR 実測 (REVISION RECORD)		DR CHK DATE		APP REV. B		
CHK. S. MANABE		APP. 28/APR/95 S. MANABE		SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-917511-2](#)