


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	Update to new Drawing format	9/11/19	J.B.	T.L.

RAYCHEM HF Tubing SCD



Dimensions mm (inches)


Size	As Supplied	As Recovered	
	Inside Diameter (D)	Inside Diameter (d)	Wall Thickness (W)
	minimum	maximum	nominal
HF-04	10.1 (0.400)	3.8 (0.150)	1.8 (0.070)
HF-07	19.0 (0.750)	5.6 (0.221)	1.8 (0.070)
HF-11	27.9 (1.100)	9.5 (0.375)	2.7 (0.105)
HF-13	33.0 (1.300)	9.5 (0.375)	2.7 (0.105)
HF-15	38.1 (1.500)	12.7 (0.500)	3.0 (0.120)
HF-17	43.1 (1.700)	12.7 (0.500)	3.0 (0.120)
HF-20	50.8 (2.000)	19.1 (0.750)	3.6 (0.140)
HF-27	68.5 (2.700)	22.9 (0.900)	3.9 (0.155)

Color: Standard Black
Reference Specification 108-120060

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT 2019 TE Connectivity

DIMENSIONS: INCHES	DWN J. Bitter	11-Sep-2019	MATERIAL -	FINISH -			
	CHK T. Licko	-	 TE Connectivity				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD T. Licko	-					
	PRODUCT SPEC 108-120060	NAME RAYCHEM HF TUBING SCD					
	APPLICATION SPEC -	SIZE A4			CAGE CODE 06090	DRAWING NO C=HF	RESTRICTED TO -
	WEIGHT 0	CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 1	REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HF-04FRX25](#)