


D




C

B

A



SCALE 1:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	-
-	-

DWN 31JUL2018 ALEX ZHANG

CHK 31JUL2018 HART HE

APVD 31JUL2018 CHRIS WANG

PRODUCT SPEC 108-106140

APPLICATION SPEC 114-137144

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME CABLE JUMPER, UNSHIELDED M8 FR TO M12 MS OR MR, A-CODE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	-	C-T40524XX00XXXX	-

SCALE 1:1 SHEET 1 OF 3 REV A


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT copyright.d8Ye-

ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SCALE 1:1



T40524X600X-00X AS SHOWN

SIDE 1 M8X1

SIDE 2 M12X1

	T40524X6003-00X	T40524X6004-00X
SIDE 1		
SIDE 2		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

-

DWN 31JUL2018 ALEX ZHANG

CHK 31JUL2018 HART HE

APVD 31JUL2018 CHRIS WANG

PRODUCT SPEC 108-106140

APPLICATION SPEC 114-137144

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

CABLE JUMPER, UNSHIELDED
M8 FR TO M12 MS OR MR, A-CODE

SIZE

A2

CAGE CODE

-

DRAWING NO

C-T40524XX00XXXX

RESTRICTED TO

-

SCALE

1:1

SHEET

2

OF

3

REV

A

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT copyright.dBTe-

ALL RIGHTS RESERVED.

TABLE 1

TECHNICAL DATA	T4052415003-00X	T4052425003-00X	T4052416003-00X	T4052426003-00X	T4052415004-00X	T4052425004-00X	T4052416004-00X	T4052426004-00X
RATED VOLTAGE	60V				30V			
RATED CURRENT	3A							
POLLUTION DEGREE	3							
OVERVOLTAGE CATEGORY	II							
MATERIAL GROUP	II							
DEGREE OF PROTECTION	IP67							

TABLE 2

WIRES: 0.25mm ² (24AWG) WIRE COLOR: 1-BROWN, 2-WHITE, 3-BLUE, 4-BLACK OD: APROX. 5.0MM	STANDARD: -001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m CUSTOMIZATION: -99X:<1.0M -XXX:>1.0M -AAX:99.XM EXAMPLE: -035=3.5M -150=15.0M -994=0.4M	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-4FR-**-M12-4MR-PUR	4	T4052426004-00X
					RPC-M8-4FR-**-M12-4MS-PUR	4	T4052425004-00X
					RPC-M8-3FR-**-M12-3MR-PUR	3	T4052426003-00X
					RPC-M8-3FR-**-M12-3MS-PUR	3	T4052425003-00X
WIRES: 0.25mm ² (24AWG) WIRE COLOR: 1-BROWN, 3-BLUE, 4-BLACK OD: APROX. 4.5MM	TOLERANCE: 0m TO 1m: ±0.05m 1m TO 3m: ±0.1m >3m: ±1.5%	FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-4FR-**-M12-4MR-PVC	4	T4052416004-00X
RPC-M8-4FR-**-M12-4MS-PVC					4	T4052415004-00X	
RPC-M8-3FR-**-M12-3MR-PVC					3	T4052416003-00X	
RPC-M8-3FR-**-M12-3MS-PVC					3	T4052415003-00X	
WIRES: 0.25mm ² (24AWG) WIRE COLOR: 1-BROWN, 3-BLUE, 4-BLACK OD: APROX. 4.5MM							
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE	△7	POS. PART NUMBER△6

NOTES:

1. TECHNICAL DATA: SEE TABLE 1

△2 CODE POSITION INDICATOR

△3 RECOMMEND TORQUE 0.4Nm

△4 RECOMMEND TORQUE 0.6Nm

△5 TE LABLE AREA.INCLUDING PN,DATE CODE...

△6 -00X: FOR CABLE LENGHT,SEE TABLE 2 AND REFFER TO LENGTH "L"

△7 -** :CABLE LENGTH,-0.5:0.5M;-1.0:1.0M;-1.5:1.5M

8. CABLE ASSEMBLY TO BE PACKAGED IN POLYBAGS;

WIRING DIAGRAM

POLE NO.	M8 A CODE	M12 A CODE
1	BROWN	BROWN
2	WHITE	WHITE
3	BLUE	BLUE
4	BLACK	BLACK

BLACK	PA66	END CAP	13
BLUE	TPU	M12 OVER-MOLDING	12
GOLD FLASH	COPPER ALLOY	MALE CONTACT	11
-	SUS	SPRING	10
NICKEL PLATED	COPPER ALLOY	M12, MALE NUT	9
BLACK	PA66	M12, MALE HSG, A CODE, 5PINS	8
-	-	CABLE	7
-	-	TE LABLE	6
BLUE	TPU	M8 RA OVERMOLDING	5
GRAY	SILICONE	O-RING	4
GOLD FLASH	COPPER ALLOY	M8 FEMALE CONTACT	3
NICKEL PLATED	COPPER ALLOY	M8 FEMALE NUT	2
BALCK COLOR	PA66	M8 FEMALE HOUSING	1
COMMENTS 备注	MATERIAL 材质	DESCRIPTION 描述	ITEM NO 序号

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

APVD
CHRIS WANG

114-137144

WEIGHT
-

CUSTOMER DRAWING

DWN
ALEX ZHANG

CHK
HART HE

APVD
CHRIS WANG

108-106140

114-137144

31 JUL 2018

31 JUL 2018

31 JUL 2018

TE Connectivity

CABLE JUMPER, UNSHIELDED
M8 FR TO M12 MS OR MR, A-CODE

SIZE
A2

CAGE CODE
-

DRAWING NO
T40524XX00XXXX

RESTRICTED TO
-

SCALE
1:1

SHEET
3 OF 3

REV
A

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4052415003-007](#)