

REV. 0
DCO 141566


COIL: @ 25°C
RESISTANCE _____ 50 OHMS \pm 10%
NOMINAL VOLTAGE _____ 5.0 VDC
MUST OPERATE _____ 2.7 VDC
MUST RELEASE _____ 1.4 VDC MAX, 0.22 VDC MIN.

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: OPERATE TIME 2 MS MAX
RELEASE TIME 4 MS MAX
CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
1A 28 VDC RESISTIVE 100,000
OPERATIONS

DR. B.D. 12/6/99 *CK* *12/6/99*

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. _____ GPL
CUST. NO. M39016/15-106M REV. _____

JMACD RELAY

JMACD-5XMS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1617351-1](#)