


COIL: @ +25 °C
 RESISTANCE 1250 OHMS ± 10%
 NOMINAL VOLTAGE 26.5-32 VDC
 MUST OPERATE 14.0 VDC
 MUST RELEASE 1.5 VDC

ENVIRONMENT:
 VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX.
 CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 4A
 28 VDC RESISTIVE 100,000
 OPERATIONS MIN.

DR. R.B. 9/14/98 CK 9/14/98

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. C. I. I. STD.
 CUST. NO.

TYPE HFW4A RELAY

HFW4A1201D00

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HFW4A1201D00](#)