

COIL: @ +25°C

RESISTANCE 1030 Ω $\pm 10\%$

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 11.4 VDC

MUST RELEASE 1.1 VDC

ENVIRONMENT:


VIBRATION 10 CPS TO 2500 CPS AT 20 g's

SHOCK 50 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES:

CUSTOMER DATA SHEET



CONTACT RATING: 2A \bar{a} 28 VDC
Resistive 100,000 operations

DR 8-12-91

CK. JmB



Communications
Instruments, Inc.

CUST. M39016/44-035L

CUST. NO. QPL

TYPE HFW RELAY

HMS 1201 S III L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HMS1201S111L](#)