


COIL: @ 25°C
 RESISTANCE 50 OHMS ± 10%
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.7 VDC
 MUST RELEASE 1.4 VDC MAX. 0.22 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX
 RELEASE TIME 4.0 MS MAX
 CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 1/8/98 CK. JERRY 1/8/98

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. OPL
 CUST. NO. M39016/18-025L

TYPE JMGAD RELAY

JMGAPD-5L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMGAPD-5L](#) [1617148-6](#)