


COIL: @ 25°C  
 RESISTANCE 3300 OHMS  $\pm$  10%  
 NOMINAL VOLTAGE 26.5 VDC  
 MUST OPERATE 14.0 VDC  
 MUST RELEASE 8.0 VDC MAX, 1.4 VDC MIN.

ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX  
RELEASE TIME 2.0 MS MAX  
CONTACT BOUNCE 1.5 MS MAX

# CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO  
1A 28 VDC RESISTIVE 100,000  
OPERATIONS

DR. R.B. 6/13/97 CK 6/13/97

**COMMUNICATIONS**  
**INSTRUMENTS, INC.**

CUST. OPL  
 CUST. NO. M39016/11-044L

TYPE "JMS" RELAY

**JMSC-26XLS**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JM5C-26XLS](#)