

TOL = ± .010

REV. 2 1/20/98

COIL: @ 25°C

RESISTANCE 200 OHMS ± 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.0 VDC

MUST RELEASE 10.1 VDC MAX, 2.3 VDC MIN.

ENVIRONMENT:

VIBRATION 10 Hz TO 2000 Hz @ 20 g's


SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 15 MS MAX.

CONTACT BOUNCE 5 MS MAX.

# CUSTOMER DATA SHEET



CONTACT RATING: 30 MICROAMPS  
30 MILLIVOLTS DC OR PEAK AC  
100,000 OPERATIONS MIN.

DR. R.B. 8/8/90 CK. 12/28/98

COMMUNICATIONS  
INSTRUMENTS, INC.

CUST. OPL  
CUST. NO. M5757/1-021

TYPE "RD" RELAY

RD6CAH2600

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[RD6CAH2600](#)