




8			7		
THIS DRAWING IS UNPUBLISHED.			RELEASED FOR PUBLICATION		
20			20		
COPYRIGHT 20			BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.		
PART NUMBER	REV	FIRST USED	POWER UNIT	FEED TYPE	
1385765-1	B	122500-1	LEADMAKER	POST FEED	
1385765-2	B	565435-5	BENCH MODEL K	PRE FEED	
1385765-3	B	354500-1	BENCH MODEL G	PRE FEED	



- 1 RECOMMENDED SPARE PARTS
- 2 GREASE LIGHTLY
- 3 GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE
- 4 16 AWG WIRE IS NOT RECOMMENDED BY TERMINAL MANUFACTURER.

-	-	-	..	-	-	129
-	-	-	-	-	-	128
2	2	2	-	354779-4	PIN, WIRE DISC, .3010	127
2	2	2	-	8-354778-0	PIN, WIRE DISC, .2895	126
1	1	1	-	986950-1	WASHER, FLAT PRECISION	125
1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	124
1	1	1	-	4088040	SF APPL INST 408-8040	123
-	-	-	..	-	-	122
-	-	-	..	-	-	121
-	-	-	..	-	-	120
-	-	-	..	-	-	119
-	-	-	..	-	-	118
1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	117
-	-	-	..	-	-	116
-	-	-	..	-	-	115
-	-	-	..	-	-	114
-	-	-	..	-	-	113
-	-	-	..	-	-	112
4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	111
-	-	-	..	-	-	110
-	-	-	..	-	-	109
-	-	-	..	-	-	108
-	-	-	..	-	-	107
-	-	-	..	-	-	106
-	-	-	..	-	-	105
1	1	1	-	992031-1	PIN, CLEVIS	104
1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	103
2	2	2	-	21017-2	SCREW, DRIVE	102
-	-	-	..	-	-	101
1	1	1	-	461264-1	PLATE, IDENTIFICATION	100
-	-	-	..	-	-	99
1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	98
-	-	-	..	-	-	97
-	-	-	..	-	-	96
-	-	-	..	-	-	95
4	4	2	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	94
2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	93
-	-	-	..	-	-	92
1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	-	-	..	-	-	90
1	1	1	-	7-21000-9	SCR, SKT HD CAP 4-40 X .188	89
-	-	-	..	-	-	88
2	2	2	-	2-21000-5	SCR, SKT HD CAP 8-32 X .250	87
1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	86
-	-	-	..	-	-	85
1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	84
-	-	-	..	-	-	83
-	-	-	..	-	-	82
1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	81
-	-	-	..	-	-	80
-	REF	-	..	455749-1	GUARD WINDOW	79
-	REF	-	..	679532-1	INSERT, GUARD	78
-	-	-	..	-	-	77
-	-	-	..	-	-	76
-	-	-	..	-	-	75
-	-	-	..	-	-	74
-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO

TERMINAL NAME: PIN					
TE PN	MANF PN	BURNDY TERMINAL - TE CRIMP SPECS			
1572454	SM14M-1TK6				
1572455	SC14M-1S6	PAD LTR	CRIMP HEIGHT		WIRE SIZE
-	-	A	.075±.002[1.91±0.05mm]		14
-	-	B	.064±.002[1.63±0.05mm]		16
-	-	C	-		-
-	-	D	-		-
SEAL PN.	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	.090 [2.29mm]	F	14-16
-	-	INSUL	-	-	-
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPL INSTRUCTIONS	SET UP GAGE	
.220 - .235	NONE	.350	408-8040	458637-1	

LOC		DIST		REVISIONS						
A	66	P	LYR	DESCRIPTION				DATE	DWN	APVD
		A		PRODUCT RELEASE				17MAY04	CMR	TE
		B		ECR-10-017836				26AUG2010	MY	TE
		</								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1385765-3](#)