

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




© COPYRIGHT 2012 By Tyco Electronics Japan G.K.

ALL RIGHTS RESERVED.

LOC
JDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED	11MAY2012	H.M	N.Y



NOTES

- MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0)
TAB CONTACT:COPPER ALLOY
RETENTION LEG:BRASS
- △ FINISH(CONTACT AREA):0.38μm MIN GOLD PLATING
OVER Ni PLATING
- △ FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL

注記




- 材料:ハウジング:ガラス入り熱可塑性
ポリエステル樹脂 (94V-0)
タブ コンタクト:銅合金
リテンション レグ:黄銅
- めっき:コンタクト:全面Ni下地
接触部:0.38μm MIN金めっき
- めっき:リテンションレグとコンタクト半田付部
:ニッケル下地の上にスズめっき

Y	NATURAL	9-1318125-2
Y	BLACK	1318125-2
X	BLACK	1318125-1
KEY	COLOR	PART No.

1318125-1
(KEYING X)1318125-2
(KEYING Y)
SCALE:2-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN I.IKEDA 07DEC1998	 TE Connectivity		
DIMENSIONS: mm		CHK N.MATSUBARA 07DEC1998			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD I.HASEGAWA 07DEC1998	NAME DOUBLE ROW HEADER ASSY 8P V-TYPE DYNAMIC D-2100D		
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		PRODUCT SPEC 108-5619 APPLICATION SPEC 114-5258 WEIGHT	SIZE A3		
MATERIAL SEE NOTE		SEE NOTE	CAGE CODE 00779		
			DRAWING NO C-1318125		
			RESTRICTED TO —		
			SCALE 4:1		
			SHEET 1 OF 2		
			REV D		



LOC J	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



SECT A-A

		回路番号			
		1	2	3	4
列番号	B	② Signal	① Ground	② Signal	② Signal
	A	② Signal	① Ground	② Signal	② Signal

POINT OF SEQUENTIAL
1-1318125-1,2



1-1318125-2
(KEYING Y)
SCALE:2-1

NOTES

1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0)
TAB CONTACT:COPPER ALLOY
RETENTION LEG:BRASS
- △ FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING
OVER Ni PLATING
- △ FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL

注 記

1. 材料:ハウジング:ガラス入り熱可塑性
ポリエステル樹脂 (94V-0)
タブ コンタクト:銅合金
リテンション レグ:黄銅
- △ めっき:コンタクト:全面Ni下地
接触部:0.38μmMIN金めっき
- △ めっき:リテンションレグとコンタクト半田付部
:ニッケル下地の上にスズめっき

Y	BLACK	1-1318125-2
X	BLACK	1-1318125-1
KEY	COLOR	PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN I.IKEDA 07DEC1998	 TE Connectivity			
DIMENSIONS: mm		CHK N.MATSUBARA 07DEC1998				
		APVD I.HASEGAWA 07DEC1998	NAME DOUBLE ROW HEADER ASSY 8P V-TYPE DYNAMIC D-2100D			
		PRODUCT SPEC 108-5619	SIZE A3			
MATERIAL SEE NOTE		APPLICATION SPEC 114-5258	CAGE CODE 00779		DRAWING NO C-1318125	
FINISH SEE NOTE		WEIGHT	RESTRICTED TO —		SCALE 4:1	
CUSTOMER DRAWING				SHEET 2 OF 2		REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1318125-1](#)