







1. 振動面加工ワシング基準
24P: 1318756 26P: 1318757
24P: 1746864 26P: 1746863

△. 図路番号: FIG. 1参照

3. 推奨刻みねじ: JIS B1115, B1122タナホイニレ, ねぐ2mm, 呼び径3. 長さ: TABLE-1参照

4. ねじ締め付トルク: 0.392N・m MAX (参考)

5. 本製品の取組は、取組説明書 No. 411-592に記述すること。

△. 3穴リットについては、 $\begin{bmatrix} -S- \\ -T- \end{bmatrix}$ を各穴のブロック中に適用すること。

△. $\begin{bmatrix} -Z- \\ -Z- \end{bmatrix}$ より、5mmの位置で測定。

△. コンタクト上士識別用マーク

△. $\begin{bmatrix} -Z- \\ -Z- \end{bmatrix}$ より2mmの位置で測定。

△. ID MARK, PART NUMBERを表示

1. PART NO. OF PLUG HOUSINGS TO BE MATED
2. 24P:1318756 26P:1318757
3. 24P:1746864 26P:1746863
△.CIRCUIT NUMBER:SEE FIG.1
3. RECOMMENDED SCREW: PAN-HEADED, TYPE 2 TAPPING SCREW,
NOMINAL DIAMETER 3mm
LENGTH: SEE TABLE 1(J1S B1115, B1122)
4. FASTENING TORQUE FOR SCREW: 0.392N·m MAX(FOR REFERENCE)
5. AS FOR THE HANDLING OF THIS PRODUCT,
FOLLOW THE INSTRUCTION SHEET No.411-5927.
△. TERTIARY DATUM: -S-, -T- OF EACH BLOCK.
△. MEASURED AT 7.5mm FROM -Z-.
△. MARKING FOR DESCENDER OF THE CONTACT FINISH
△. MEASURE AT 2mm FROM -Z-.
△. ID MARK, PART NUMBER INDICATED.

プリント基板板厚 (mm) THICKNESS OF PCB (mm)	1.2	1.6
固定用ねじ着下長さ (mm) NOMINAL LENGTH OF SCREW (mm)	5	6

	PLASTIC BOX 黒箱	PLASTIC TUBE プラスチックチューブ	62	16.72	∅2.4	PBT	SELECTIVE-TIN (MATTE)	-	1-6, 27,28,31,32	-	7-26 29,30,33-50	-	-	NATURAL (自然色)	NATURAL (自然色)	6318750-3
	PLASTIC BOX 黒箱	PLASTIC TUBE プラスチックチューブ	△9	15.68	∅2.63	SPS	SELECTIVE-TIN (MATTE)	-	1-6, 27,28,31,32	-	9-14,20-23,25 29,30,37 39-41,44,47	7,8,15-19,24,26 33-36,38,42 43,45,46,48-50	-	BLACK (黒色)	BLACK (黒色)	1-1318750-8
	CARTON BOX タンボ・黒箱	PLASTIC TUBE プラスチックチューブ	8	16.72	∅2.4	PBT	SELECTIVE-TIN (MATTE)	-	1-6, 27,28,31,32	-	-	7-26 29,30,33-50	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-6
	PLASTIC BOX 黒箱	PLASTIC TUBE プラスチックチューブ	8	16.72	∅2.4	PBT	SELECTIVE-TIN (MATTE)	-	1-6, 27,28,31,32	-	-	7-26 29,30,33-50	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-5
	PLASTIC BOX 黒箱	PLASTIC TUBE プラスチックチューブ	5	16.72	∅2.4	PBT	SELECTIVE-TIN (MATTE)	-	1-6, 27,28,31,32	-	9-14,20-23,25 29,30,37 39-41,44,47	7,8,15-19,24,26 33-36,38,42 43,45,46,48-50	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-4
	CARTON BOX タンボ・黒箱	PLASTIC TUBE プラスチックチューブ	5	16.72	∅2.4	PBT	SELECTIVE-TIN (MATTE)	-	1-6, 27,28,31,32	-	9-14,20-23,25 29,30,37 39-41,44,47	7,8,15-19,24,26 33-36,38,42 43,45,46,48-50	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-3
	CARTON BOX タンボ・黒箱	PLASTIC TUBE プラスチックチューブ	△4	15.68	∅2.63	SPS	SELECTIVE-TIN (MATTE)	-	1-6, 27,28,31,32	-	-	7-26 29,30,33-50	-	BLACK (黒色)	NATURAL (自然色)	1-1318750-2
	PLASTIC BOX 黒箱	PLASTIC TUBE プラスチックチューブ	△4	15.68	∅2.63	SPS	SELECTIVE-TIN (MATTE)	-	1-6, 27,28,31,32	-	-	7-26 29,30,33-50	-	BLACK (黒色)	NATURAL (自然色)	1-1318750-1
	CARTON BOX タンボ・黒箱	PLASTIC TUBE プラスチックチューブ	△6	16.72	∅2.4	PBT	SELECTIVE-TIN (MATTE)	1-6, 27,28,31,32	-	7-26,29,30 33-50	-	-	-	NATURAL (自然色)	NATURAL (自然色)	1-1318750-0
	PLASTIC BOX 黒箱	PLASTIC TUBE プラスチックチューブ	△7	16.72	∅2.4	PBT	SELECTIVE-TIN (MATTE)	-	1-6, 27,28,31,32	-	29,48	7-26,30 33-47,49,50	-	NATURAL (自然色)	NATURAL (自然色)	1318750-9
OBSOLETE	PLASTIC BOX 黒箱	PLASTIC TUBE プラスチックチューブ	3	16.72	∅2.4	PBT	SELECTIVE-TIN	-	-	1-6, 27,28,31,32	9-14,20-23,25 29,30,37 39-41,44,47	-	7,8,15-19,24,26 33-36,38,42 43,45,46,48-50	NATURAL (自然色)	NATURAL (自然色)	1318750-7
OBSOLETE	CARTON BOX タンボ・黒箱	PLASTIC TUBE プラスチックチューブ	3	16.72	∅2.4	PBT	SELECTIVE-TIN	-	-	1-6, 27,28,31,32	9-14,20-23,25 29,30,37 39-41,44,47	-	7,8,15-19,24,26 33-36,38,42 43,45,46,48-50	NATURAL (自然色)	NATURAL (自然色)	1318750-6
	PLASTIC BOX 黒箱	PLASTIC TUBE プラスチックチューブ	2	16.72	∅2.4	PBT	PRE-TIN TIN LEAD	-	-	1-6, 27,28,31,32	7-26, 29,30,33-50	-	-	NATURAL (自然色)	NATURAL (自然色)	1318750-3
	CARTON BOX タンボ・黒箱	PLASTIC TUBE プラスチックチューブ	1	16.72	∅2.4	PBT	PRE-TIN	-	-	1-6, 27,28,31,32	-	-	7-26, 29,30,33-50	NATURAL (自然色)	NATURAL (自然色)	1318750-2
	PLASTIC BOX 黒箱	PLASTIC TUBE プラスチックチューブ	1	16.72	∅2.4	PBT	PRE-TIN	-	-	1-6, 27,28,31,32	-	-	7-26, 29,30,33-50	NATURAL (自然色)	NATURAL (自然色)	1318750-1
	OUTER 外装	INNER 内装	MARKING (マーキング)	WEIGHT (g)	V	HOUSING MATERIAL (ハウジング材料)	SOLDERING SIDE 半田付け側	SELECTIVE GOLD	SELECTIVE-TIN (BRIGHT)	PRE-TIN	SELECTIVE GOLD	SELECTIVE-TIN (BRIGHT)	PRE-TIN	TINE PLATE COLOR (タインプレート色)	HOUSING COLOR (ハウジング色)	PART NUMBER (型番)
	PACKING STYLE 梱包形態							CONTACT SIDE 接触部側						CONTACT FINISH (仕上げ)		

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN M. HAYASHI	27APR2000	 TE Connectivity			
DIMENSIONS: DIM. 附		CHK N. SAI	27APR2000		NAME 025/090 SERIES 50POSITION CAP ASSEMBLY		
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIM. = ± 0.3		APP'D N. SAI	27APR2000			SIZE	CAGE CODE
		PRODUCT SPEC 108-5667 APPLICATION SPEC 114-5250 WEIGHT		A1	00779	RESTRICTED TO —#—	
MATERIAL CONTACT-BRASS HOUSING-SEE TABLE FINISH RE: SEE TABLE		CUSTOMER DRAWING		POLE	2-1	SHEET 1 OF 2	
				REV. A			


4

3


2

1

LOC	DIST	REVISIONS 変更				
		P	LTR	DESCRIPTION	ECN	DATE
J	-			SEE 1 OF 2		



CAP ASSEMBLY AND PLUG ASSEMBLY ENGAGEMENT DRAWING
キャップアッセンブリ & プラグアッセンブリ 嵌合図

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. HAYASHI 27APR2000		 TE Connectivity					
		CHK N. SAI 27APR2000							
DIMENSIONS: 単位: ㎜ mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3		NAME 025/090 SERIES 50POSITION CAP ASSEMBLY					
		0-PLC ±		SIZE A3					
		1-PLC ±0.1							
		2-PLC ±0.01							
		3-PLC ±0.001							
		4-PLC ±0.000J							
ANGLES ±3'00"		PRODUCT SPEC 製品規格 SEE 1 OF 2		CAGE CODE 00779		DRAWING NO 番号 C=1318750		RESTRICTED TO —//—	
APPLICATION SPEC 取付適用規格 SEE 1 OF 2		WEIGHT SEE 1 OF 2							
MATERIAL 材料 SEE 1 OF 2		FINISH 仕上 SEE 1 OF 2		CUSTOMER DRAWING					
				SCALE 尺度 2:1		SHEET 2 OF 2		REV A3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1318750-0](#)