

4

3

2

1

| LOC | DIST | REVISIONS | | | | |
|-----|------|-----------|-----|----------------------|-----------|---------|
| | | P | LTR | DESCRIPTION | DATE | APVD |
| J | - | | A | RELEASED | 06JAN2010 | R.K N.Y |
| | | | B | ADDITION NEW PART NO | 22NOV2010 | M.M N.Y |
| | | | | | | |
| | | | | | | |

D

C

B


A

D




C

B

A



RECOMMEND PC BOARD HOLE PATTERN : CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1
推奨基板取付寸法 : コネクタ搭載面 (非累積公差)
PC基板厚 : 1.0~1.6±0.1




1. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC POLYESTER (94V-0)
COLOR: BLACK
CONTACT: PRE-TIN COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

1. 材料: ハウジング: ガラス入り熱可塑性ポリエステル樹脂 (94V-0) 色: 黒
コンタクト: 錫めっき銅合金
リテンションレグ: 錫めっき銅合金

2. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。

| | | | | | |
|-----|-----|---|------|------|-------------|
| 20 | X | 9 | 18.0 | 22.6 | 1-1554590-0 |
| 10 | X | 4 | 8.0 | 12.6 | 1-1554590-5 |
| POS | KEY | n | A | B | PART NO |



20POS(X-KEY): 1-1554590-0

| | | | | |
|---|--|----------------------------|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. | | DWN R. KIKUCHI 24DEC2009 | Tyco Electronics Corporation Kawasaki, Japan | |
| DIMENSIONS: 単位: 概 mm | | CHK N. YAMASAKI 24DEC2009 | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5° | | APVD N. YAMASAKI 24DEC2009 | NAME 名称 DYNAMIC D1100D 2.0mm PITCH HDR ASSY (V-TYPE) BLACK PRE-TIN PLATE 4-20POS | |
| 0-PLC ± | | PRODUCT SPEC 108-78298 | | |
| 1-PLC ± | | APPLICATION SPEC 114-5377 | SIZE A3 CAGE CODE 00779 DRAWING NO 1554590 RESTRICTED TO - | |
| 2-PLC ± | | WEIGHT - | | |
| 3-PLC ± | | CUSTOMER DRAWING | SCALE 4:1 SHEET 1 OF 2 REV B | |
| 4-PLC ± | | | | |
| ANGLES ± | | | | |
| FINISH 仕上 | | | | |
| MATERIAL 材料 1 | | | | |


4

3



2

1

| LOC | DIST | REVISIONS | | | | |
|-----|------|-----------|-----|------------------|------|------|
| | | P | LTR | DESCRIPTION | DATE | APVD |
| J | - | | - | SEE SHEET 1 OF 2 | - | - |
| | | | | | | |
| | | | | | | |
| | | | | | | |



1-1554590-5
10POS(X-KEY)



| | | | | | | |
|--|--|----------------------------------|---|-------------------------|--------------------|----------|
| THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. | | DWN R. KIKUCHI 24DEC2009 | Tyco Electronics Corporation Kawasaki, Japan | | | |
| DIMENSIONS: mm | | CHK N. YAMASAKI 24DEC2009 | | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD N. YAMASAKI 24DEC2009 | NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) BLACK PRE-TIN PLATE 4-20POS | | | |
| 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± | | PRODUCT SPEC 108-78298 | | | | |
| MATERIAL | | APPLICATION SPEC 114-5377 | SIZE A3 | | | |
| FINISH | | WEIGHT - | | | | |
| CUSTOMER DRAWING | | | CAGE CODE 00779 | DRAWING NO C-1554590 | RESTRICTED TO - | |
| | | | SCALE 4:1 | SHEET 2 | OF 2 | REV B |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1554590-5](#)