







LOC	DIST	REVISIONS 変更						
		P	LTR	DESCRIPTION		DATE	DWN	APVD
J	-		O	RELEASED	FJA0-0144-03	28MAR2003	RN	HY
			A	REVISED	ECR-10-005857	13MAY10	SF	KB
			A1	REVISED	ECR-10-022322	01NOV10	AY	TH
			A2	REVISED	ECR-15-011109	13AUG15	AY	TH




1. APPLICABLE WIRE RANGE ;
AVSS 0.3, 0.5, 0.3f, 0.5fmm²
CAVS 0.3, 0.5mm²
CHFUS 0.35, 0.50mm²
HFTUF 2cX0.5mm²
2. APPLICATION SPEC ; 114-5315
3. APPLICATOR FEED ; 18mm
△ TIN PLATING AREA

1. 適用電線 ;
AVSS 0.3, 0.5, 0.3f, 0.5fmm²
CAVS 0.3, 0.5mm²
CHFUS 0.35, 0.50mm²
HFTUF 2cX0.5mm²
2. 取付適用規格 ; 114-5315
3. アプリケータ送りピッチ ; 18mm
△ すずめっき範囲

SELECTIVE GOLD	1612124-3
FINISH	PART NUMBER

WIRE RANGE 総合電線断面積		0.22-0.56mm ²		INSULATION DIA 被覆外径		Ø0.95-1.7	
				TE Connectivity			
NAME 名称		ImmDIA SOCKET CONTACT					
SIZE	CAGE CODE	DRAWING NO 番号				RESTRICTED TO	
A3	00779	C-1612124				-	
		SCALE 尺度		SHEET		OF	REV
		5:1		1		1	A2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	28MAR2003
		R. NAGAI	
		CHK	28MAR2003
		T. HAYASHI	
		APVD	28MAR2003
		H. YAMAGAMI	
DIMENSIONS: 単位: 耗 mm		PRODUCT SPEC 製品規格	
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		108-5679
	一般公差 ±0.2		APPLICATION SPEC
	0 PLC ±		取付適用規格
	1 PLC ±0.1		114-5315
	2 PLC ±0.01		WEIGHT
	3 PLC ±0.001		0.36 g
4 PLC ±0.000J		CUSTOMER DRAWING	
ANGLES ±1.00°			
MATERIAL 材料	FINISH 仕上		
COPPER Alloy	SELECTIVE GOLD		

DIMENSIONS: 単位: 耗		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		一般公差 ±0.2	
		0-PLC ±	
		1-PLC ±0.1	
		2-PLC ±0.01	
		3-PLC ±0.001	
		4-PLC ±0.0001	
		ANGLES ±1'00"	
MATERIAL 材料		FINISH 仕上	
COPPER Alloy		SELECTIVE GOLD	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1612124-3](#)