

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL INTERNATIONAL RIGHTS RESERVED.



© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

LOC



DIST

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REDRAWN W/CHANGE	ECR-10-014585	12JUL10	TS KB



B-B



C-C




THIS DIMENSION IS CONTROLLED
WITH MATING FORCE
この寸法は嵌合力によって
規定する。

A-A

GENERAL TOLERANCE

0<* < 10 : ±0.2
10<* < 30 : ±0.25
30<* < 100 : ±0.3
ANGLES : ±0.3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

BRASS
黄銅 0.32t

DWN

T.SHINOHARA

12JUL10

CHK

K.BETSUI

12JUL10

APVD

K.BETSUI

PRODUCT SPEC

APPLICATION SPEC

114-5082

WEIGHT

-

CUSTOMER DRAWING

WIRE RANGE
包合電線断面積1.25~3mm² (AWG #16~#12)INSULATION DIA
被覆外形

2.5~4.1mm

Tyco Electronics Corporation
Kawasaki, Japan

NAME

250 SERIES RECEPTACLE CONTACT
FOR SEALED CONNECTOR

SIZE

CAGE CODE

DRAWING NO

A300779 C-171632

RESTRICTED TO

-

SCALE 1:1

SHEET 1 OF 1

REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[171632-1](#) [171632-1 \(Loose Piece\)](#)