



- NOTES:
- △ FOR POWER CIRCUITS (4 POS.)
 - △ FOR SIGNAL CIRCUITS (12 POS.)
 - 3. ACCOMMODATED CONTACTS ARE
STRIP P/N 170311, 170312, 170484
L.P. P/N 170313, 170314, 170485
 - 4. FEMALE HSG P/N IS 172068
 - 5. RPOD.SPEC 108-5125, APPLICATION SPEC 114-5044

- 注記:
- △ 電源回路用 (4極)
 - △ 信号回路用 (12極)
 - 3. 本ハウジングに使用するコンタクトは
連鎖状 型番 170311, 170312, 170484
バラ状 型番 170313, 170314, 170485
 - 4. 本ハウジングに適合する雌ハウジングは 172068
 - 5. 製品規格番号 108-5125
取付 適用規格番号 114-5044

番号 (NUMBER)			
C	ADD -3	J83-6955	Y.I.K.S. 3/18/83
B ₁	REVISED	J81-5961	S.M. 3/28/81
B	REVISED	J80-5597	S.M. 8/2/80
A ₁	REVISED	J9-5095	S.M. 1/16/79
A	REDRAWN W/CHANGE	J9-5038	S.M. 1/12/79
LTR.	変更 (REVISION RECORD)		DR. CHK. DATE

C-172059

組立部品 (REQUIRED PER ASSEMBLY)		① 1979 年 日本エー・エム・ピー株式会社 AMP 社の諸製品は特許又は特許出願中		② 1979 BY AMP (Japan), Ltd. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING		参考図面 (CUSTOMER COPY) (REFERENCE ONLY)	
材料 (MATERIAL)		被覆電線断面積 (WIRE RANGE)		TRADE MARK		日本エー・エム・ピー株式会社 TOKYO, JAPAN	
仕上 (FINISH)		被覆外径 (INSULATION DIA.)		分類 (CLASS)		型式 (TYPE)	
色: 青色 GLASS FILLED PBT 94V-0 (ガラス入り)		mm ² (AWG)		mm (IN)		一般公差 (TOLERANCE EXCEPT AS NOTED)	
仕上 (FINISH)		mm (IN)		1-1		1-1	
DR. K. Yano 8/8/79		CHK. J. Fujita 1/12/79		DE. J. Fujita 2/14/79		APP. J. Fujita 2/14/79	
記事 (DESCRIPTION)		名称 (NAME)		16 極 雄 ハウジング, トロワ-コネクタ		16 POS. MALE HSG, DRAWER CONNECTOR	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[172059-3](#)