




断面 A-A
SECT.



断面 C-C
SECT.



断面 D-D
SECT.

注記

- 製品規格 : 108-5174
- 取付通用規格 : 114-5076
- 相当品 P/N : 181270-1

NOTES

- PRODUCT SPEC. : 108-5174
- APPLICATION SPEC. : 114-5076
- SIMILAR TO 181270-1

752936-1 HAND TOOL No 手動工具 No	172788-1 STRIP P/N 連鎖状端子	0.38 Au PL. ON CONTACT AREA - OTHERS ARE NI PL. 接触部 0.38μ以上の部分のみ Au 残部 ニッケルめっき	172790-1 型番 P/N
		0.1982 BY AMP Japan Ltd. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.	参考図面 (CUSTOMER COPY) REFERENCE ONLY
		MATERIAL PHOS-BR. 以青銅 0.22t	TRADE MARK AMP 日本アイ・エム・ピー株式会社 TOKYO, JAPAN
		SEE TABLE 表参照	WIRE CLASS 0.12 ~ 0.38 (AWG) #22 - #26
		INSULATION DIA 0.9 ~ 1.55 (mm) IN	WIRE TYPE //
0, REVISED (ECN No J84-7505) J.G. S.M. 2-13-84	0, RELEASED (ECN No J82-6500) S.M.	一般公差 TOLERANCE EXCEPT AS NOTED ±0.4 ±0.15 ±1.0	LOC SIZE 番号 NO J A C-172790 0,
DR S. Manabe APR-28-82	DE S. Manabe APR-28-82	REC. CONTACT, AMP MOD. MOD. II CRIMP-ON · SNAP-IN アンプ モジュ モデル II · 圧着型 コンタクト	
CHK T. Taguchi 5-17-82	APP T. Taguchi 5-17-82		

単位：此 DIMENSIONS IN MM DO NOT SCALE PRINT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[172790-1](#)