





D

C


B

A



- △X 面から2mmの範囲で測定
2. 嵌合相手ハウジング型 174516, 174515, 174514, 917992, 917989, 917981
3. 推奨取付ねじ: JIS B1115, B1112 タッピンねじ, なべ2種
呼び径3, 長さ6mm以下 (締付けトルク: 0.4N-m (4kg-cm) 以下)
4. 適用製品規格番号: 108-5280, 108-5342

△回路番号:
パワー回路 ①～⑩
シグナル回路 ⑪～⑥④




△適用製品型番のプリフィックス及びIDマークを
カラーホットマークにて表示

1. MUST BE KEPT BETWEEN X AND 2
2. THE MATING PLUG HSG PART NUMBER: 174516, 174515, 174514, 917992, 917989, 917981
3. RECOMMENDED MOUNTING SCREW: 3mm DIA, 6mm LENGTH (MAX.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1112
(TIGHTENING TORQUE: 0.4N-m (4kg-cm) MAX.)
4. APPLICABLE PRODUCT SPEC NO.: 108-5280, 108-5342

△CIRCUIT NUMBER
POWER CIRCUIT NO. ①～⑩
SIGNAL CIRCUIT NO. ⑪～⑥④
△INDICATED PREFIX AND ID MARK OF PRODUCT P/N BY COLOR HOT MARK

OBSOLETE	59	SELECTIVE-TIN (MATT)	SELECTIVE GOLD × 8	-	49~56	GRAY 灰色	9-5174518-6
			PRE-TIN × 56				
	51	SELECTIVE-TIN (MATT)	SELECTIVE GOLD × 64	1~16	17~64	GRAY 灰色	1-5174518-6
			PRE-TIN × 16				
	52	SELECTIVE-TIN (MATT)	SELECTIVE GOLD × 48	-	17~64	YELLOW 黄色	2-5174518-7
			PRE-TIN × 8				
	59	SELECTIVE-TIN (MATT)	SELECTIVE GOLD × 8	-	49~56	YELLOW 黄色	9-5174518-7
			PRE-TIN × 56				
	56	SELECTIVE-TIN (MATT)	SELECTIVE GOLD × 9	14, 16	57~63	NATURAL 自然色	6-5174518-1
			SELECTIVE-TIN (BRIGHT) × 55				
	9	TIN-LEAD	SELECTIVE GOLD × 8	-	49~56	GRAY 灰色	9-174518-7
			PRE-TIN × 56				
	9	TIN-LEAD	SELECTIVE GOLD × 12	-	33, 34, 36~38, 40, 43, 56, 59~56	YELLOW 黄色	8-174518-7
			PRE-TIN × 52				
	7	TIN-LEAD	SELECTIVE GOLD × 16	-	33~40, 49~56	YELLOW 黄色	7-174518-7
			PRE-TIN × 48				
	6	TIN-LEAD	SELECTIVE GOLD × 9	14, 16	57~63	NATURAL 自然色	6-174518-1
			PRE-TIN × 55				
	5	TIN-LEAD	SELECTIVE GOLD × 24	-	17~24, 33~40, 49~56	YELLOW 黄色	5-174518-7
			PRE-TIN × 40				
	4	TIN-LEAD	SELECTIVE GOLD × 22	-	23, 24, 31~48, 52, 57	YELLOW 黄色	4-174518-7
			PRE-TIN × 42				
	3	TIN-LEAD	SELECTIVE GOLD × 52	7~10	17~64	YELLOW 黄色	3-174518-7
			PRE-TIN × 12				
	3	TIN-LEAD	SELECTIVE GOLD × 52	7~10	17~64	GRAY 灰色	3-174518-6
			PRE-TIN × 12				
	2	TIN-LEAD	SELECTIVE GOLD × 48	-	17~64	YELLOW 黄色	2-174518-7
			PRE-TIN × 16				
	2	TIN-LEAD	SELECTIVE GOLD × 48	-	17~64	GRAY 灰色	2-174518-6
			PRE-TIN × 16				
	2	TIN-LEAD	SELECTIVE GOLD × 48	-	17~64	NATURAL 自然色	2-174518-1
			PRE-TIN × 16				
	1	TIN-LEAD	SELECTIVE GOLD × 64	1~16	17~64	GRAY 灰色	1-174518-7
			PRE-TIN × 64				
	1	TIN-LEAD	SELECTIVE GOLD × 64	1~16	17~64	GRAY 灰色	1-174518-6
			PRE-TIN × 64				
OBSOLETE	0		PRE-TIN × 64	-	-	YELLOW 黄色	174518-7
			PRE-TIN × 64				
OBSOLETE	0		PRE-TIN × 64	-	-	GRAY 灰色	174518-6
			PRE-TIN × 64				
△MARKING マーキング		SOLDERING SIDE 半田付け面	CONTACT SIDE 接触面	POWER CIRCUIT NO. パワー回路	SIGNAL CIRCUIT NO. シグナル回路	COLOR 色	PART NUMBER 製品型番
		CONTACT FINISH コンタクト仕上		GOLD PLATED CIRCUIT NO. 金めっき回路番号			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SHINOHARA 12FEB08	 TE Connectivity				
		CHK K. BETSUI 12FEB08					
DIMENSIONS: 単位: 寸 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称	64POSITION CAP HOUSING ASSEMBLY 040/070 SERIES HYBRID I/O CONNECTOR			
		0 PLC ±			APVD K. BETSUI 12FEB08 PRODUCT SPEC 製品規格 SHEET NOTE 4		
		1 PLC ±					
		2 PLC ±					
		4 PLC ±					
ANGLES	±	APPLICATION SPEC 取付通規格	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL 材料	FINISH 仕上	WEIGHT	A1	00779	174518	-	
HOUSING : PBT CONTACT : BRASS		CUSTOMER DRAWING		SCALE 比率	2:1	SHEET 1 of 1	REV H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-174518-6](#)