







- △1 A 面より2mmの範囲で測定。
△2 相手ハウジングと所定の機能を満たして嵌合できること。
3. プリント基板への取付けは、JIS B1115又は1122, M3×6ナベ (2種又は4種)のタッピンネジで締付けた後ハンダ付けする。
4. 嵌合相手ハウジング型番：174952
- △1 TO BE MEASURED BETWEEN A AND 2.
△2 TO BE MATED WITH PLUG HSG SMOOTHLY.
3. TO BE USE M3 TAPPING SCREW JIS B1115 OR 1122 (TYPE2 OR 4) BEFORE SOLDER.
4. APPLIDE PLUG HOUSING PART NUMBER：174952

OBSOLETE	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 20	NATURAL 自然色	2-5174960-1
	SELECTIVE-TIN	PRE-TIN × 20	NATURAL 自然色	3-174960-1
	TIN-LEAD	SELECTIVE GOLD × 20	NATURAL 自然色	2-174960-1
	PRE-TIN × 20		YELLOW 黄色	1-174960-7
	PRE-TIN × 20		GRAY 灰色	1-174960-6
	PRE-TIN × 20		NATURAL 自然色	1-174960-1
	SOLDERING SIDE 半田付け面	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 26JUN07	TE Connectivity	
DIMENSIONS: 単位： 転 mm		CHK K.BETSUI 26JUN07		
		APVD K.BETSUI 26JUN07	NAME 名称 .070 SERIES MULTI-LOCK I/O CONN 20POSITION CAP HSG ASSEMBLY VERTICAL TYPE	
		PRODUCT SPEC 製品規格 108-5216		
TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差 0<≦ 10 : ±0.2 10<≦ 30 : ±0.25 30<≦ 100 : ±0.3 ANGLE : ±3°		APPLICATION SPEC 取付適用規格 412-5520	SIZE A2 CAGE CODE 00779 DRAWING NO 番号 C=174960	
		MATERIAL 材料 HOUSING: PBT CONTACT: BRASS		
		FINISH 仕上 -	RESTRICTED TO -	
		WEIGHT 10.6 g	SCALE 尺度 2:1 SHEET 1 OF 1 REV E3	
		CUSTOMER DRAWING		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-174960-6](#)