





D

C

B

A



- 1 TO BE MEASURED BETWEEN [A] AND 2
2 TO BE MATED WITH PLUG HOUSING SMOOTHLY
3. TO BE USE M3 TAPPING SCREW JIS B1115 OR 1122 (TYPE 2 OR 4) BEFORE SOLDER
4. APPLIED PLUG HOUSING PART NUMBER; 173851, 173853

- 1 [A] 面から2mmの範囲で測定
2 相手ハウジングと所定の機能を満たして嵌合できること
3. プリント基板への取付けは、JIS B1115 又は 1122, M3×6ナベ (2種又は4種) のタッピンネジで締付けた後ハンダ付けする
4. 嵌合相手ハウジング型番; 173851, 173853

TOLERANCE UNLESS OTHERWISE SPECIFIED:
一般公差

0 < x ≤ 10	: ±0.2
10 < x ≤ 30	: ±0.25
30 < x ≤ 100	: ±0.3
ANGLE	: ±3°
角度	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

HOUSING; PBT
CONTACT; BRASS

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

DWN
T.SHINOHARA
30AUG2012

CHK
K.BETSUI
30AUG2012

APVD
K.BETSUI
30AUG2012

PRODUCT SPEC
108-5216

APPLICATION SPEC
-

WEIGHT
15 g

CUSTOMER DRAWING

SELECTIVE-TIN (MATTE)

SELECTIVE GOLD × 30

NATURAL 自然色

2-5174961-1

PRE-TIN × 30

NATURAL 自然色

1-174961-1

SOLDERING SIDE 半田付け面

CONTACT SIDE 接触部側

COLOR 色

PART NUMBER 製品型番

CONTACT FINISH コンタクト仕上

TE Connectivity

070 SERIES MULTI-LOCK CONNECTOR
30POSITION CAP HOUSING ASSEMBLY
V-TYPE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=174961

RESTRICTED TO
-

SCALE
2:1

SHEET
1 of 1

REV
F4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-174961-1](#)