





REVISONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D7	REVISED	ECR-16-003344	25OCT2016	KF	HY



(MOUNTING DIMENSIONS FOR P. C. BORD,
TOLERANCE±0. 1)
プリント基板取付寸法図
一般公差； ±0.1
(公差は累積しないこと)
(NON ACCUMULATE TOLERANCE)

- NOTES
- △ MUST BE KEPT BETWEEN [X] AND 2
 - 2 THE MATING PLUG HSG.PART NUMBER;
174516, 174515, 174514, 917992, 917989, 917981
 - 3 RECOMMENDED MOUNTING SCREW; 3mmDIA, 6mmLENGTH(MAX.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS
B1115, B1122
(TIGHTENING TORQUE; 0. 4N. m(4Kg-cm)MAX.)
 - 4 APPLICABLE PRODUCT. SPEC NO. 108-5280, 108-5342
 - △ CIPCUIT NUMBER ; SEE FIG. 1
POWER CIPCUIT NO. ① ~ ⑩
SIGNAL CIPCUIT NO. ⑪ ~ ⑥④
 - △ MARKING FOR DISCERNMENT OF THE CONTACT FINISH

- 注記
- △ [X] 面から2mmの範囲で測定
 - 2. 嵌合相手ハウジング型 174516, 174515, 174514, 917992, 917989, 917981
 - 3. 推奨取付ねじ； JIS B1115, B1122 タッピンねじ, なべ2種
呼び径3, 長さ6mm以下 (締付トルク； 0.4N.m(4Kg-cm)以下)
 - 4. 適用製品規格番号； 108-5280, 108-5342
 - △ 回路番号； FIG.1参照のこと
パワー回路； ① ~ ⑩
シグナル回路； ⑪ ~ ⑥④
 - △ コントクト仕上識別マーク






FIG.1

59	---	PRE-TIN x 5L SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 10	⑭ - ⑰	⑤⑦ ~ ⑥④	GRAY 灰色	9-5178764-6
55	---	PRE-TIN x 4L SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 22	---	⑦-②③ ③-④⑤ ④⑥-⑤⑦	YELLOW 黄色	5-5178764-7
54	---	PRE-TIN x 4L SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 22	---	③ ②③ ①①-④⑤ ⑤⑦ ⑥⑦	YELLOW 黄色	4-5178764-7
53	---	PRE-TIN x 4L SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 52	⑦ ~ ⑰	⑦ ~ ⑥④	GRAY 灰色	3-5178764-6
52	---	PRE-TIN x 16 SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 48	---	⑦ ~ ⑥④	GRAY 灰色	2-5178764-6
52	---	PRE-TIN x 16 SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 48	---	⑦ ~ ⑥④	NATURAL 自然色	2-5178764-1
51	---	PRE-TIN x 16 SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 64	① - ⑬	⑦ ~ ⑥④	GRAY 灰色	1-5178764-6
8	---	PRE-TIN x 52 TIN-LEAD / SELECTIVE GOLD x 12	---	③③③③-③④③⑤③⑤⑤⑤	YELLOW 黄色	8-178764-7
7	---	PRE-TIN x 4L TIN-LEAD / SELECTIVE GOLD x 16	---	③③-③④ ③④-③⑤	YELLOW 黄色	7-178764-7
6	---	PRE-TIN x 55 TIN-LEAD / SELECTIVE GOLD x 9	⑬ - ⑰	⑤⑦ ~ ⑥③	NATURAL 自然色	6-178764-1
5	---	PRE-TIN x 4L TIN-LEAD / SELECTIVE GOLD x 22	---	⑦-②③ ③-④⑤ ④⑥-⑤⑦	YELLOW 黄色	5-178764-7
4	---	PRE-TIN x 4L TIN-LEAD / SELECTIVE GOLD x 22	---	③ ②③ ①①-④⑤ ⑤⑦ ⑥⑦	YELLOW 黄色	4-178764-7
3	---	PRE-TIN x 12 TIN-LEAD / SELECTIVE GOLD x 52	⑦ ~ ⑰	⑦ ~ ⑥④	YELLOW 黄色	3-178764-7
3	---	PRE-TIN x 12 TIN-LEAD / SELECTIVE GOLD x 52	⑦ ~ ⑰	⑦ ~ ⑥④	GRAY 灰色	3-178764-6
2	---	PRE-TIN x 16 TIN-LEAD / SELECTIVE GOLD x 48	---	⑦ ~ ⑥④	YELLOW 黄色	2-178764-7
2	---	PRE-TIN x 16 TIN-LEAD / SELECTIVE GOLD x 48	---	⑦ ~ ⑥④	GRAY 灰色	2-178764-6
2	---	PRE-TIN x 16 TIN-LEAD / SELECTIVE GOLD x 48	---	⑦ ~ ⑥④	NATURAL 自然色	2-178764-1
1	---	TIN-LEAD SELECTIVE GOLD x 64	① - ⑬	⑦ ~ ⑥④	YELLOW 黄色	1-178764-7
1	---	TIN-LEAD SELECTIVE GOLD x 64	① - ⑬	⑦ ~ ⑥④	GRAY 灰色	1-178764-6
0	---	PRE-TIN x 64	---	---	YELLOW 黄色	178764-7
A	⑬ ⑭	PRE-TIN x 62	---	---	NATURAL 自然色	178764-2
0	---	PRE-TIN x 64	---	---	NATURAL 自然色	178764-1
△ MARKING マーキング	NO CONTACT CIRCUIT NO. △ 欠番	FINISH OF CONTACT タブ仕上 (本数)	POWER CIRCUIT NO. パワ-回路	SIGNAL CIRCUIT NO. シグナル回路	HOUSING COLOR ハウジング色	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位：mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED

MATERIAL
材料

HOUSING ; PBT
CONTACT ; BRASS

DWN
T. SHINOHARA

CHK
K. BETSUI

APVD
K. BETSUI

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT
28.4 g

CUSTOMER DRAWING

03AUG05

03AUG05

03AUG05

NAME
氏名

SIZE
A1

CAGE CODE
00779

DRAWING NO
178764

RESTRICTED TO
REV
D7

TE Connectivity

64POS CAP. HOUSING ASSY
.040/.070 SERIES HYBRID I/O CONN.

SCALE
2:1

SHEET
1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-178764-6](#)