

D

C

B





A

D

C

B

A



(MOUNTING DIMENSIONS FOR P. C. BOARD,
TOLERANCE±0.1)
プリント基板取付寸法図
一般公差；±0.1
(公差は累積しないこと)
(NON ACCUMULATE TOLERANCE)

- NOTES
- MUST BE KEPT BETWEEN [X] AND 2
 - THE MATING PLUG HSG.PART NUMBER;
174516, 174515, 174514, 917992, 917989, 917981
 - RECOMMENDED MOUNTING SCREW; 3mmDIA, 6mmLENGTH(MAX.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS
B1115, B1122
(TIGHTENING TORQUE; 0.4N. m(4Kg-cm)MAX.)
 - APPLICABLE PRODUCT SPEC NO. 108-5280, 108-5342
- △ CIRCUIT NUMBER ; SEE FIG. 1
POWER CIRCUIT NO. ① ~ ⑩
SIGNAL CIRCUIT NO. ⑪ ~ ⑥④
- △ MARKING FOR DISCERNMENT OF THE CONTACT FINISH

- 注記
- [X] 面から2mmの範囲で測定
 - 嵌合相手ハウジング型 174516, 174515, 174514, 917992, 917989, 917981
 - 推奨取付ねじ; JIS B1115, B1122 タッピンねじ, なべ2種
呼び径3, 長さ6mm以下 (締付トルク; 0.4N.m(4Kg-cm)以下)
 - 適用製品規格番号; 108-5280, 108-5342
- △ 回路番号; FIG.1参照のこと
パワー回路; ① ~ ⑩
シグナル回路; ⑪ ~ ⑥④
- △ コンタクト仕上識別マーク






FIG.1

59	---	PRE-TIN x 5L SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 10	⑭・⑰	⑤⑦ ~ ⑥④	GRAY 灰色	9-5178764-6
55	---	PRE-TIN x 4L SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 22	---	⑦-②③ ③-④⑤ ④⑥-⑤⑦	YELLOW 黄色	5-5178764-7
54	---	PRE-TIN x 4L SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 22	---	③ ②③ ①①-④⑤ ⑤⑦ ⑥⑦	YELLOW 黄色	4-5178764-7
53	---	PRE-TIN x 4L SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 22	⑦ ~ ⑰	⑦ ~ ⑥④	GRAY 灰色	3-5178764-6
52	---	PRE-TIN x 16 SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 4.8	---	⑦ ~ ⑥④	GRAY 灰色	2-5178764-6
52	---	PRE-TIN x 16 SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 4.8	---	⑦ ~ ⑥④	NATURAL 自然色	2-5178764-1
51	---	PRE-TIN x 16 SELECTIVE TIN (MATTE) / SELECTIVE GOLD x 4.8	①・⑬	⑦ ~ ⑥④	GRAY 灰色	1-5178764-6
8	---	PRE-TIN x 5L TIN-LEAD / SELECTIVE GOLD x 12	---	③③③③-③④③③③③③③	YELLOW 黄色	8-178764-7
7	---	PRE-TIN x 4L TIN-LEAD / SELECTIVE GOLD x 16	---	③③-④③ ④③-⑤⑦	YELLOW 黄色	7-178764-7
6	---	PRE-TIN x 5L TIN-LEAD / SELECTIVE GOLD x 9	⑬・⑰	⑤⑦ ~ ⑥③	NATURAL 自然色	6-178764-1
5	---	PRE-TIN x 4L TIN-LEAD / SELECTIVE GOLD x 22	---	⑦-②③ ③-④⑤ ④⑥-⑤⑦	YELLOW 黄色	5-178764-7
4	---	PRE-TIN x 4L TIN-LEAD / SELECTIVE GOLD x 22	---	③ ②③ ①①-④⑤ ⑤⑦ ⑥⑦	YELLOW 黄色	4-178764-7
3	---	PRE-TIN x 12 TIN-LEAD / SELECTIVE GOLD x 52	⑦ ~ ⑰	⑦ ~ ⑥④	YELLOW 黄色	3-178764-7
3	---	PRE-TIN x 12 TIN-LEAD / SELECTIVE GOLD x 52	⑦ ~ ⑰	⑦ ~ ⑥④	GRAY 灰色	3-178764-6
2	---	PRE-TIN x 16 TIN-LEAD / SELECTIVE GOLD x 4.8	---	⑦ ~ ⑥④	YELLOW 黄色	2-178764-7
2	---	PRE-TIN x 16 TIN-LEAD / SELECTIVE GOLD x 4.8	---	⑦ ~ ⑥④	GRAY 灰色	2-178764-6
2	---	PRE-TIN x 16 TIN-LEAD / SELECTIVE GOLD x 4.8	---	⑦ ~ ⑥④	NATURAL 自然色	2-178764-1
1	---	TIN-LEAD SELECTIVE GOLD x 64	①・⑬	⑦ ~ ⑥④	YELLOW 黄色	1-178764-7
1	---	TIN-LEAD SELECTIVE GOLD x 64	①・⑬	⑦ ~ ⑥④	GRAY 灰色	1-178764-6
0	---	PRE-TIN x 64	---	---	YELLOW 黄色	178764-7
A	⑬ ⑭	PRE-TIN x 62	---	---	NATURAL 自然色	178764-2
0	---	PRE-TIN x 64	---	---	NATURAL 自然色	178764-1
△ MARKING マーキング	NO CONTACT CIRCUIT NO. △ 欠番	FINISH OF CONTACT タブ仕上 (本数)	POWER CIRCUIT NO. パワ-回路	SIGNAL CIRCUIT NO. シグナル回路	HOUSING COLOR ハウジング色	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.
DWN T. SHINOHARA 03AUG05
CHK K. BETSUI 03AUG05
APVD K. BETSUI 03AUG05
NAME 氏名

DIMENSIONS:
単位: 寸
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED
公差

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL
材料
HOUSING ; PBT
CONTACT ; BRASS

FINISH
仕上
SEE TABLE

WEIGHT
重量
28.4 g

SIZE
寸法
A1

CAGE CODE
軍用規格
00779

DRAWING NO
図番
178764

RESTRICTED TO
制限
-

CUSTOMER DRAWING

SCALE
尺度
2:1

SHEET
枚数
1 of 1

REV
改訂
D7

TE Connectivity

64POS CAP. HOUSING ASSY
.040/.070 SERIES HYBRID I/O CONN.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-178764-6](#)