





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	ECN	DATE	APVD
J	-	A1		PART NO ADDITION		22MAR2007	M.M D.M
		A2		DRAFTING ERROR	ECR-07-005648	23OCT2007	M.M S.M
		B		REVISED	ECR-07-025215	07NOV2008	M.M A.O
		C		REVISED		25NOV2009	Y.O T.K



1. MATERIAL: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
3. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".

1. 材料: ガラス入り熱可塑性ポリエステル樹脂(94V-0), 色: 黒
2. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。
3. Y KEY形状はX KEY形状と左右対称

40	Y	19	38.0	40.9	42.6	2-1827863-0
40	X	19	38.0	40.9	42.6	1-1827863-0
34	Y	16	32.0	34.9	36.6	2-1827863-7
34	X	16	32.0	34.9	36.6	1-1827863-7
32	X	15	30.0	32.9	34.6	1-1827863-6
30	X	14	28.0	30.9	32.6	1-1827863-5
28	X	13	26.0	28.9	30.6	1-1827863-4
26	Y	12	24.0	26.9	28.6	2-1827863-3
26	X	12	24.0	26.9	28.6	1-1827863-3
24	X	11	22.0	24.9	26.6	1-1827863-2
22	X	10	20.0	22.9	24.6	1-1827863-1
POS	KEY	n	A	B	C	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T. KUDO 16MAR2005	Tyco Electronics Corporation Kawasaki, Japan			
DIMENSIONS: 単位: 概 mm		CHK D. MITSUGI 23AUG2005	NAME DYNAMIC DII00D 2.0mmPITCH REC HSG 22-40POS			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5° 0-PLC ± 1-PLC ±0.1 2-PLC ±0.02 3-PLC ±0.005 4-PLC ±0.0005 ANGLES ± FINISH 仕上		APVD D. MITSUGI 23AUG2005				
MATERIAL 材料		PRODUCT SPEC 製品規格 108-78268, 78298	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
		APPLICATION SPEC 取付適用規格 114-5377	A300779C-1827863			
		WEIGHT	SCALE 2:1 SHEET 1 OF 3 REV C			
		CUSTOMER DRAWING				

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR
















DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 3



22POS(X-KEY): 1-1827863-1

26POS(X-KEY): 1-1827863-3

28POS(X-KEY): 1-1827863-4

30POS(X-KEY): 1-1827863-5

32POS(X-KEY): 1-1827863-6

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL

FINISH

DWN 16MAR2005

CHK T. KUDO

D. MITSUGI 23AUG2005

APVD D. MITSUGI 23AUG2005

PRODUCT SPEC

108-78268, 78298

APPLICATION SPEC

114-5377

WEIGHT

-

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation
Kawasaki, Japan

NAME

DYNAMIC D1100D 2.0mmPITCH
REC HSG
22-40POS

SIZE

CAGE CODE

DRAWING NO







RESTRICTED TO

A300779C-1827863

SCALE 2:1

SHEET 2 OF 3

REV C



34POS(X-KEY): 1-1827863-7

24POS(X-KEY): 1-1827863-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1827863-0](#)