
















LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	-			SEE SHEET 1 OF 3			



22POS(X-KEY):
3-1871056-1(YELLOW)

26POS(X-KEY):
1-1871056-3(NATURAL)

28POS(X-KEY):
5-1871056-4(RED)

32POS(X-KEY):
1-1871056-6(NATURAL)

30POS(X-KEY):
1-1871056-5(NATURAL)
3-1871056-5(YELLOW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

DWN
T. KUDO 21APR2005

CHK
D. MITSUGI 23AUG2005

APVD
D. MITSUGI 23AUG2005

PRODUCT SPEC
108-78298

APPLICATION SPEC
114-5377

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
DYNAMIC 1100D 2.0mmPITCH
HDR ASSY (V-TYPE)
TIN PLATE-COLOR 22-40POS

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1871056

RESTRICTED TO
-

SCALE
2:1

SHEET
2

OF
3

REV
E1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1871056-0](#)