

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2006

© COPYRIGHT 2006

BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

J

DIST

REVISIONS

変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED ECR-10-016030	02AUG2010	T.T	T.M

CAVITY MARK
(ALPHABET:CAPITAL LETTER)

2.5Xn=C

2.5

3.3

CIRCUIT NO

0168321

A

B

E

1.MATERIAL:GLASS FILED THERMO PLASTIC POLYESTER(94V-0)

2.COLOR :EXCLUDING BLACK

3.THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

4.THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".

1.材料:ガラス入り熱可塑性ポリエステル樹脂(94V-0)

2.色 :黒以外

3.文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。

4.Y KEY形状は、X KEY形状と左右対称

4-1939028-□ : YELLOW (Y-KEY)

3-1939028-□ : YELLOW (X-KEY)

2-1939028-□ : NATURAL (Y-KEY)

1-1939028-□ : NATURAL (X-KEY)

LOGO MARK

SERIES CODE

KEYING:X

tyco D1200

D

ROW ID

12.45

11.3

8.6

9.4

9

B

A

2.5Xn=C

2.5

3.3

1.6

1-1939028-0

20POS:NATURAL,X-KEY

3-1939028-0

20POS:YELLOW,X-KEY

20	9	Y	8.3	15.9	22.5	25.9	27.6	4-1939028-0(YELLOW)
20	9	X	8.3	15.9	22.5	25.9	27.6	3-1939028-0(YELLOW)
20	9	Y	8.3	15.9	22.5	25.9	27.6	2-1939028-0(NATURAL)
20	9	X	8.3	15.9	22.5	25.9	27.6	1-1939028-0(NATURAL)
12	5	Y	8.3	15.9	12.5	15.9	17.6	4-1939028-6(YELLOW)
12	5	X	8.3	15.9	12.5	15.9	17.6	3-1939028-6(YELLOW)
12	5	Y	8.3	15.9	12.5	15.9	17.6	2-1939028-6(NATURAL)
12	5	X	8.3	15.9	12.5	15.9	17.6	1-1939028-6(NATURAL)
10	4	Y	3.3	10.9	10.0	13.4	15.1	4-1939028-5(YELLOW)
10	4	X	3.3	10.9	10.0	13.4	15.1	3-1939028-5(YELLOW)
10	4	Y	3.3	10.9	10.0	13.4	15.1	2-1827864-5(NATURAL)
10	4	X	3.3	10.9	10.0	13.4	15.1	1-1939028-5(NATURAL)
8	3	Y	3.3	10.9	7.5	10.9	12.6	4-1939028-4(YELLOW)
8	3	X	3.3	10.9	7.5	10.9	12.6	3-1939028-4(YELLOW)
8	3	Y	3.3	10.9	7.5	10.9	12.6	2-1939028-4(NATURAL)
8	3	X	3.3	10.9	7.5	10.9	12.6	1-1939028-4(NATURAL)
6	2	Y	3.3	8.4	5.0	8.4	12.6	4-1939028-3(YELLOW)
6	2	X	3.3	8.4	5.0	8.4	10.1	3-1939028-3(YELLOW)
6	2	Y	3.3	8.4	5.0	8.4	10.1	2-1939028-3(NATURAL)
6	2	X	3.3	8.4	5.0	8.4	10.1	1-1939028-3(NATURAL)
4	1	Y	3.1	8.4	2.5	5.9	-	4-1939028-2(YELLOW)
4	1	X	3.1	7.6	2.5	5.9	-	3-1939028-2(YELLOW)
4	1	Y	3.1	7.6	2.5	5.9	-	2-1939028-2(NATURAL)
4	1	X	3.1	7.6	2.5	5.9	-	1-1939028-2(NATURAL)
POS	n	KEY	A	B	C	D	E	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: 純

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差 ±0.3, ±3°

0-PLC ±

1-PLC ±

2-PLC ±

3-PLC ±

4-PLC ±

ANGLES ±

FINISH 仕

MATERIAL

材料

DWN

M.MAEBASHI

19APR2006

CHK

T.KUDO

19APR2006

APVD

D.MITSUGI

19APR2006

PRODUCT SPEC

108-78268,78298

APPLICATION SPEC

114-5377

WEIGHT

CUSTOMER DRAWING

Tyco
Electronics

Tyco Electronics Corporation
Kawasaki, Japan

NAME

名称

DYNAMIC D1200D 2.5mmPITCH
REC HSG COLOR
4-20POS

SIZE

CAGE CODE

DRAWING NO

REV

RESTRICTED TO

A200779

C-1939028

SCALE

6:1

SHEET

1




OF

3




REV

C




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J				SEE SHEET 1		



1-1939028-2
4POS:NATURAL,X-KEY
3-1939028-2
4POS:YELLOW,X-KEY



1-1939028-3
6POS:NATURAL,X-KEY
3-1939028-3
6POS:YELLOW,X-KEY









1-1939028-4
8POS:NATURAL,X-KEY
3-1939028-4
8POS:YELLOW,X-KEY

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN M. MAEBASHI 19APR2006	Tyco Electronics Corporation Kawasaki, Japan		
DIMENSIONS: 単位: 純 mm		CHK T. KUDO 19APR2006	NAME 名称 DYNAMIC DI200D 2.5mmPITCH REC HSG COLOR 4-20POS		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH 仕		APVD D. MITSUGI 19APR2006	SIZE A200779		
MATERIAL 材料		PRODUCT SPEC 108-78268,78298 APPLICATION SPEC 114-5377 WEIGHT	DRAWING NO C-1939028		
CUSTOMER DRAWING		RESTRICTED TO			SCALE 6:1
		SHEET 2 OF 3			REV C

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2006
© COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
J				SEE SHEET 1		



1-1939028-5
10POS:NATURAL,X-KEY

3-1939028-5
10POS:YELLOW,X-KEY

1-1939028-6
12POS:NATURAL,X-KEY

3-1939028-6
12POS:YELLOW,X-KEY

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN M. MAEBASHI CHK T. KUDO APVD D. MITSUGI	19APR2006 19APR2006 19APR2006	Tyco Electronics Corporation Kawasaki, Japan	
DIMENSIONS: 単位: 純 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH 仕		NAME DYNAMIC DI200D 2.5mmPITCH REC HSG COLOR 4-20POS	
MATERIAL 材料		PRODUCT SPEC 108-78268,78298 APPLICATION SPEC 114-5377 WEIGHT		SIZE A200779	CAGE CODE C-1939028
CUSTOMER DRAWING		SCALE 1:1		SHEET 3	OF 3
				REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1939028-3](#)