










1437288-4 (旧型番: 3900135-2612)
6437288-4 (旧型番: -)

注 1。一般公差： ± 0.3

- △ 材質 キャップハウジング：熱可塑性ポリエステル樹脂
整列板：熱可塑性ポリエステル樹脂
ピンコンタクト：黄銅／ニッケル下地、金めっき（接点部）
はんだめっき（基板側）

△3. 当箇所製造日管理番号（ロット番号）を印字する。

4. 基板取付けねじ
JIS B 1122 十字穴付きタッピンねじ なべ2種 3×L (L=6.5+基板厚)
先端溝付き及び溝無し (亜鉛メッキ)
上記以外のねじを使用の場合、別途打ち合わせの事。

-  材質 キャップハウジング：熱可塑性ポリエステル樹脂
整列板：熱可塑性ポリエステル樹脂
ピンコンタクト：黄銅 / ニッケル下地、金めっき（接点部）
すずめっき（基板側）

6. 嵌合相手型番：TABLE-1 参照

5-6447223-1	3-1437290-8
6437288-4	
1437288-4	
5-6447223-0	3-1437290-7
5-1447223-0	
PART NUMBER	MATING PLUG ASSEMBLY

TABLE-1

NOTE. 1. GENERAL TOLERANCE : ± 0.3

- △ MATERIAL
- CAP HOUSING : POLYESTER
- ARRANGEMENT PLATE : POLYESTER
- PIN CONTACT : BRASS GOLD PLATING OVER Ni PLATING (CONTACT PART)
BRASS TIN-LEAD PLATING OVER Ni PLATING (SOLDERING PART)

3. MANUFACTURED DATE CONTROL NO.(LOT NO.)

AS FOLLOWING IS INDICATED.


4. MOUNTING SCREW

JIS B 1122 CROSS RECESSED PAN HEAD TAPPING SCREW (ZINC PLATING)
TYPE 2 3xL (L=6.5xBOARD THICKNESS)

-  MATERIAL
- CAP HOUSING : POLYESTER
- ARRANGEMENT PLATE : POLYESTER
- PIN CONTACT : BRASS GOLD PLATING OVER Ni PLATING (CONTACT PART)
BRASS TIN PLATING OVER Ni PLATING (SOLDERING PART)

6. PART NUMBER OF PLUG ASSEMBLY TO BE MATED: SEE TABLE-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN (A.ISHIJIMA)		100CT00		 TE Connectivity	
DIMENSIONS: 単位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED. 一般公差		NAME 名称		SUPERSEAL コネクタ(下ロック) キャップハウジング 26極 ASS'Y	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 製品規格		SUPER SEAL CONNECTOR	
MATERIAL 材料		FINISH 仕上		APPLICATION SPEC 取付適用規格		CAP HOUSING ASS'Y 26P (UNDER LOCK)	
SEE TABLE		WEIGHT —		SIZE A2		CAGE CODE 00779	
				DRAWING NO 番号		RESTRICTED TO	
				C-5-1447223-0		—	
CUSTOMER DRAWING				SCALE 尺度		SHEET	
				2:1		1 of 3	
						REV A1	



A

6.

D

C

B

A

D

C

B

A

注 1。一般公差：±0.3

- △2材質 キャップハウジング：熱可塑性ポリエステル樹脂
 整列板：熱可塑性ポリエステル樹脂
 ピンコンタクト：黄銅/ニッケル下地、金めっき（接点部）
 はんだめっき（基板側）

- △3△当箇所製造日管理番号（ロット番号）を印字する。
- 4。基板取付けねじ
JIS B 1122 十字穴付きタッピンねじ なべ2種 3xL≤6.5+基板厚）
先端溝付き及び溝無し（亜鉛メッキ）
上記以外のねじを使用の場合、別途打ち合わせの事。

- △5材質 キャップハウジング：熱可塑性ポリエステル樹脂
 整列板：熱可塑性ポリエステル樹脂
 ピンコンタクト：黄銅/ニッケル下地、金めっき（接点部）
 すずめっき（基板側）

- 6。嵌合相手型番：4-1437290-0（34極）、3-14373290-7（26極）

NOTE. 1。GENERAL TOLERANCE：±0.3

- △2 MATERIAL
CAP HOUSING：POLYESTER
ARRANGEMENT PLATE：POLYESTER
PIN CONTACT：BRASS GOLD PLATING OVER Ni PLATING (CONTACT PART)
 BRASS TIN LEAD PLATING OVER Ni PLATING (SOLDERING PART)






- △3△MANUFACTURED DATE CONTROL NO.(LOT NO.)
AS FOLLOWING IS INDICATED.

- 4。MOUNTING SCREW
JIS B 1122 CROSS RECESSED PAN HEAD TAPPING SCREW
TYPE 2 3xL (L=6.5xBOARD THICKNESS)

- △5 MATERIAL
CAP HOUSING：POLYESTER
ARRANGEMENT PLATE：POLYESTER
PIN CONTACT：BRASS GOLD PLATING OVER Ni PLATING (CONTACT PART)
 BRASS TIN PLATING OVER Ni PLATING (SOLDERING PART)

(ZINC PLATING)

- 6。PART NUMBER OF PLUG ASSEMBLY TO BE MATED：4-1437290-0（34Pos.）、3-1437290-7（26Pos.）



6437288-5	△5	—	本 図
OBSOLETE	1437288-5	△2	3900135-6011
Part No.	Old Part No.	REMARK	
型 番	旧 型 番	備 考	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN (A.ISHIJIMA) 100CT00		CHK	
DIMENSIONS: 単位： 桁 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED. 一般公差		APVD	
0 PLC ±		1 PLC ±		PRODUCT SPEC 製品規格	
2 PLC ±		3 PLC ±		APPLICATION SPEC 取付適用規格	
4 PLC ±		ANGLES ±		WEIGHT	
FINISH 仕上		—		CUSTOMER DRAWING	
MATERIAL 材料		SEE TABLE		SCALE 2:1	
				SHEET 3 of 3	
				REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-6447223-0](#)