


DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION




NOTES :

1. PRODUCT SPECIFICATION: 108-19043



2. PACKAGING: ON PLASTIC TUBES, BOXED

3 CONTACT AREA TO BE LUBRICATED
WITH LUBRICATION (ELECTROLUBE 2X)
MIN. 110mg/1000 CONTACTS
MAX. 200mg/1000 CONTACTS

4 CONTACT SPRING MAY HAVE
SPHERICAL SHAPE IN THIS AREA,
HOLLOW FORM NOT PERMITTED.
SPHERICAL SHAPE DIM. AT
CONTACT POINT AS DETAILED



SECTION A-A



BOARD TO BOARD
CONTACTS FOR
0,8 MIN. DIA HOLE

CONTACT: TOTAL AREA
3,0 µm MIN TIN
OVER 1,25 µm MIN NICKEL
UNDERLAYER

HOUSING: THERMOPLASTIC
POLYESTER 20% GLF
UL 94V0
COLOUR: BROWN
CONTACT: PH. BRONZE H06
(CuSn4)

1-100317-5

FINISH				MATERIAL		PART NUMBER	
D3	ET00-0047-04	D. C.	C. T.	05MAR2004	CUSTOMER DRAWING C COPYRIGHT 19- BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U. S. AND FOREIGN AND/OR PATENTS PENDING. THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION , 19 tyco Electronics tyco Electronics AMP Italia S.p.A. C.so F.lli Cervi, 15 - Collegno (TO)	FOR REFERENCE ONLY WILL NOT BE UPDATED	
D2	ET00-0147-03	D. C.	C. T.	21AUG2003			
D1	ET00-0115-03	D. C.	C. T.	04JUL2003			
D	ET00-0068-03	P. B	D. C	09-05-03			
C	H-9473	R. D.	N. S.	24-01-92			
B	H-9302	R. D.	N. S.	19-12-91	NAME 15 POS. 2,54 CENTRE AMP EDGE CONN. ASS'Y DUAL LOADED WITH B. T. B. CONTACT		
A	H-9302	J. v. L	N. S.	07-11-91			
LTR.	REVISION RECORD	DR.	CHK.	DATE			
DR.:	S. MEEUWSEN.	CHK.:	N. SOUSA.	APP.:	L. v. SOEST.	DWG. No.	REV. LTR.
DATE:	27 MAR 1991	DATE:	07. 11. 91	DATE:	26. 11. 91	C-100317	D3
						SHEET	SIZE
						1 OF 1	A3

8

7

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-100317-5](#)