





DO NOT SCALE
DIMENSIONS IN mm

METRIC


THIRD ANGLE
PROJECTION



NOTES:

1. PRODUCT SPECIFICATION: 108-19041
2. PACKAGING: ON PLASTIC TUBES, BOXED

SECTION A-A



CONTACT: 0,4µm MIN SELECTIVE
GOLD PLTD ON MATING CONTACT
AREA AND 3,0µm MIN TIN PLTD
ON CONTACT POST, OVER 1,25µm
MIN NI PLTD UNDERLAYER

HOUSING: THERMOPLASTIC
POLYESTER 20% GF, UL94-v0
COLOUR GREEN
CONTACT: 1 PH. BRONZE H06

1-166088-3

CUSTOMER
DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

tyco
Electronics

tyco Electronics AMP Italia S.p.A.
C.so F.lli Cervi, 15 - Collegno (TO)

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION JULY 1986

© COPYRIGHT 1986 BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

H2	ET00-0047-04	D.C.	C.T.	05MAR2004
H1	ET00-0115-03	D.C.	C.T.	24JUN2003
H	ET00-0068-03	P.B	D.C	9-5-03
G	-	-	-	12-6-89
LTR.	REVISION RECORD	DR.	CHK.	DATE

DR. C. SOUSA	DATE 08-07-86
CHK. J. BROEKSTEEG	DATE 08-07-86
APP. L. V. SOEST	DATE 09-07-86

WIRE RANGE	NAME
INSUL. RANGE	13 POS. AMP-EDGE CONN., 2.54 PITCH SINGLE LOADED WITH B.T.B. CONTACTS
SIZE A3	SHEET 1 OF 1
DRAWING NO C-166088	REV. LTR. H2

8

7

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-166088-3](#)