



Raychem


TE Internal #: 170605-000

Cable Transitions & Breakouts, Y Shape, 3 Branches , 100, 100,

Adhesive Precoat Adhesive Requirement

[View on TE.com >](#)

Wire Protection & Management > Heat Shrink Molded Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**

Number of Branches & Legs: **3**

Material Code: **100**

Material Systems Code: **100**

Adhesive Requirement: **Adhesive Precoat**

## Features

### Product Type Features

Molded Part Shape	Y Shape
Size Code	023

### Configuration Features

Number of Branches & Legs	3
Adhesive Requirement	Adhesive Precoat

### Body Features

Material	Low Fire Hazard Material
Material Code	100
Material Systems Code	100

### Dimensions

Inside Diameter Range (Leg 2)	6.1 – 13.2 mm [.24 – .52 in]
Inside Diameter Range (Body)	12.4 – 26.9 mm [.49 – 1.06 in]
Inside Diameter Range (Leg 1)	6.1 – 13.2 mm [.24 – .52 in]

### Usage Conditions

Flammability	Low Fire Hazard
Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]

### Operation/Application

--	--



Emission Features	Halogen-Free
Power Cable Accessory	No

### Other

Molded Part Shape Code	382A
Fluid & Chemical Resistance	Long-Term Fluid Exposure at High Temperatures
Adhesive Options	/180 Precoat

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CJ2087-000  
HL2010E-KIT-120V

## Customers Also Bought



TE Part #631516-000  
Bulbous Heat Shrink Boots: Lipped,  
Straight



TE Part #117451-000  
222K121-25/225-0




TE Part #6418370001  
TMS-SCE-1/8-2.0-4




TE Part #BTH1-11-13-1-ZB-SB  
BTH1-11-13-1-ZB-SB




TE Part #2332756-2  
MT Ferrule Kit,V66.5 Rcpt,Pins,24-F,  
MM



TE Part #AAB1521-00  
91H1-09-06-1-C-HE100



TE Part #AAB1592-00  
91H1-11-05-1-C-HE100



TE Part #W326TF11-23SA  
W3 PLUG ASSEMBLY WITH REAR  
THREAD SIZE 1

## Documents

### Product Drawings

382A023-100/180-0

English

### Datasheets & Catalog Pages

1654025\_Sec4\_-100

English

### Raychem Molded Parts Visual Guide

English

### Product Environmental Compliance

Safety Datasheet

Safety Datasheet

English

Safety Datasheet

French

Safety Datasheet



German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[382A023-100/180-0](#)