



4

3

2

1



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		A	PART NOS ADDED, NOTES UPDATED	10JUL2015	PS	JK



91.44	25	2-1986343-5
87.63	24	2-1986343-4
83.82	23	2-1986343-3
80.01	22	2-1986343-2
76.20	21	2-1986343-1
72.39	20	2-1986343-0
68.58	19	1-1986343-9
64.77	18	1-1986343-8
60.96	17	1-1986343-7
57.15	16	1-1986343-6
53.34	15	1-1986343-5
49.53	14	1-1986343-4
45.72	13	1-1986343-3
41.91	12	1-1986343-2
38.10	11	1-1986343-1
34.29	10	1-1986343-0
30.48	9	1986343-9
26.67	8	1986343-8
22.86	7	1986343-7
19.05	6	1986343-6
15.24	5	1986343-5
11.43	4	1986343-4
7.62	3	1986343-3
3.81	2	1986343-2
DIM "A"	NO. OF POS.	PART NO.

NOTES:

- MATERIALS AND FINISH:
HOUSING : PA 6.6, UL 94-V0, COLOR: BLACK
TERMINAL : PHOSPHOR BRONZE, TIN PLATED
- SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS.
- NOT CUMULATIVE TOLERANCE.
- OPERATING TEMPERATURE RANGE : -40°C TO +110°C
- ELECTRICAL:
CURRENT RATING: 11A
VOLTAGE RATING : 300V
WIRE SIZE RANGE: 30 - 14 AWG
CONTACT RESISTANCE: <15m Ohm
INSULATION RESISTANCE: 1000M Ohm (500V DC)



RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 30JAN2008	 TE Connectivity			
		CHK C RICHARD 1/30/08				
		APVD C RICHARD 1/30/08	NAME			
		PRODUCT SPEC	TERMINAL BLOCK HEADER ASSEMBLY 90 DEGREE, CLOSED ENDS 3.81mm PITCH			
		APPLICATION SPEC	—			
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-1986343	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1		REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[1-1986343-0](#) [1-1986343-3](#) [1-1986343-2](#) [1-1986343-5](#) [1-1986343-4](#) [1-1986343-1](#) [1-1986343-9](#) [1-1986343-7](#) [1-1986343-6](#) [1986343-8](#) [1986343-9](#) [2-1986343-4](#) [1986343-6](#) [2-1986343-3](#) [1986343-7](#) [2-1986343-5](#) [2-1986343-0](#) [1986343-2](#) [1986343-3](#) [2-1986343-2](#) [1986343-5](#) [2-1986343-1](#)