



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
020	RELEASED	07/23/92	<i>[Signature]</i>

NOTES:
1. CAPTURED CENTER CONTACT

DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A		
CENTER CONTACT HOUSING	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290		
COMPONENT	MATERIAL	FINISH		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES • 1/64 • .005 • 1° These drawings and specifications are the property of Omri Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	DRAWN BY <i>[Signature]</i> DATE 4/16/92	AMP AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599		
	CHECKED BY <i>[Signature]</i> 07/23/92			
	APPROVED BY <i>[Signature]</i> 04/17/92			
	USE ASS'Y PROCEDURE			
NO. A.P. <u>N/A</u>	TITLE OSMT JACK TO OSM JACK ADAPTER			
	SIZE B	CODE IDENT NO. 26805	2380-2240-00	REV 020
	SCALE 10 : 1		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1055694-1](#)